

# SAC-4P-M12MS/ 0,3-511/M12FR FB - Sensor/actuator cable



1552667

<https://www.phoenixcontact.com/us/products/1552667>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, Special mixture on PVC base, black RAL 9005, Plug straight M12, coding: A, on Socket angled M12, coding: A, cable length: 0.3 m

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1552667                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BF03                           |
| Product key                          | AF1CCA                         |
| GTIN                                 | 4046356156004                  |
| Weight per piece (including packing) | 30.7 g                         |
| Weight per piece (excluding packing) | 30.7 g                         |
| Customs tariff number                | 85444290                       |
| Country of origin                    | DE                             |

# SAC-4P-M12MS/ 0,3-511/M12FR FB - Sensor/actuator cable



1552667

<https://www.phoenixcontact.com/us/products/1552667>

## Technical data

### Product properties

|                      |                          |
|----------------------|--------------------------|
| Product type         | Sensor/actuator cable    |
| Application          | Food processing industry |
| Number of positions  | 4                        |
| No. of cable outlets | 1                        |
| Shielded             | no                       |
| Coding               | A                        |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | HB                                          |
| Seal material                          | NBR                                         |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Stainless steel                             |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 48 V AC                    |
|                       | 60 V DC                    |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Conductor connection

|                   |                        |
|-------------------|------------------------|
| Tightening torque | 0.4 Nm (M12 connector) |
|-------------------|------------------------|

### Connector

#### Connection 1

# SAC-4P-M12MS/ 0,3-511/M12FR FB - Sensor/actuator cable



1552667

<https://www.phoenixcontact.com/us/products/1552667>

|                     |                   |
|---------------------|-------------------|
| Type                | Plug straight M12 |
| Number of positions | 4                 |
| Coding type         | A                 |


## Connection 2

|                     |                   |
|---------------------|-------------------|
| Type                | Socket angled M12 |
| Number of positions | 4                 |
| Coding type         | A                 |

## Cable/line

|              |       |
|--------------|-------|
| Cable length | 0.3 m |
|--------------|-------|

## PVC black FDA [511]

|                                 |                                                                                                |
|---------------------------------|------------------------------------------------------------------------------------------------|
| Dimensional drawing             |             |
| Number of positions             | 4                                                                                              |
| Shielded                        | no                                                                                             |
| Cable type                      | PVC black FDA [511]                                                                            |
| Conductor structure signal line | 42x 0.10 mm                                                                                    |
| AWG signal line                 | 22                                                                                             |
| Conductor cross section         | 0.34 mm²                                                                                       |
| Wire diameter incl. insulation  | 1.52 mm ±0.05 mm                                                                               |
| External cable diameter         | 5.20 mm ±0.2 mm                                                                                |
| Outer sheath, material          | Special mixture on PVC base                                                                    |
| External sheath, color          | black RAL 9005                                                                                 |
| Conductor material              | Bare Cu litz wires                                                                             |
| Material wire insulation        | PVC                                                                                            |
| Single wire, color              | brown, white, blue, black                                                                      |
| Overall twist                   | 4 wires, twisted                                                                               |
| Nominal voltage, cable          | 300 V                                                                                          |
| Test voltage                    | 1500 V                                                                                         |
| Resistance to oil               | good oil-resistance                                                                            |
| Other resistance                | UV resistant<br>Silicone-free                                                                  |
| Special properties              | FDA compliant                                                                                  |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)<br>-5 °C ... 90 °C (Cable, flexible installation) |

## Environmental and real-life conditions

# SAC-4P-M12MS/ 0,3-511/M12FR FB - Sensor/actuator cable



1552667

<https://www.phoenixcontact.com/us/products/1552667>

## Ambient conditions

|                                                                   |                                   |
|-------------------------------------------------------------------|-----------------------------------|
| Degree of protection                                              | IP65                              |
|                                                                   | IP67                              |
|                                                                   | IP68                              |
|                                                                   | IP69K                             |
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 105 °C (Plug / socket) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |


# SAC-4P-M12MS/ 0,3-511/M12FR FB - Sensor/actuator cable

1552667

<https://www.phoenixcontact.com/us/products/1552667>


## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



M12 x 1 socket, angled

# SAC-4P-M12MS/ 0,3-511/M12FR FB - Sensor/actuator cable

1552667

<https://www.phoenixcontact.com/us/products/1552667>

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

# SAC-4P-M12MS/ 0,3-511/M12FR FB - Sensor/actuator cable

1552667

<https://www.phoenixcontact.com/us/products/1552667>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

# SAC-4P-M12MS/ 0,3-511/M12FR FB - Sensor/actuator cable



1552667  
<https://www.phoenixcontact.com/us/products/1552667>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
|-------------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31251501 |
|-------------|----------|

# SAC-4P-M12MS/ 0,3-511/M12FR FB - Sensor/actuator cable



1552667  
<https://www.phoenixcontact.com/us/products/1552667>

## Environmental product compliance

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| China RoHS                             |                                                                                                                                                                                                                                   |
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC                          |                                                                                                                                                                                                                                   |
| REACH candidate substance (CAS No.)    | No substance above 0.1 wt%                                                                                                                                                                                                        |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)