

SAC-4P-10,0-100/M 8FS - Sensor/actuator cable



1577590

<https://www.phoenixcontact.com/us/products/1577590>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PUR/PVC, gray RAL 7001, free cable end, on Socket straight M8, coding: A, cable length: 10 m

Commercial data

Item number	1577590
Packing unit	1 pc
Minimum order quantity	25 pc
Product key	AF1BCA
GTIN	4046356459389
Weight per piece (including packing)	336.52 g
Weight per piece (excluding packing)	222.22 g
Country of origin	DE

SAC-4P-10,0-100/M 8FS - Sensor/actuator cable



1577590

<https://www.phoenixcontact.com/us/products/1577590>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	4
No. of cable outlets	1
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket straight M8
Number of positions	4
Coding type	A

Cable/line

Cable length	10 m
--------------	------


PUR/PVC gray [100]

SAC-4P-10,0-100/M 8FS - Sensor/actuator cable



1577590

<https://www.phoenixcontact.com/us/products/1577590>

Dimensional drawing	
	
Cable weight	32 kg/km
Number of positions	4
Shielded	no
Cable type	PUR/PVC gray [100]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross section	0.25 mm²
Wire diameter incl. insulation	1.32 mm ±0.02 mm
External cable diameter	4.70 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation) ≥ 0.38 mm (Outer cable sheath) approx. 3.80 mm ±0.1 mm (Inner sheath)
Overall twist	4 wires, twisted
Max. conductor resistance	max. 78 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	47 mm
Smallest bending radius, movable installation	47 mm
Dynamic load capacity (bending)	Max. bending cycles: 2000000, Bending radius: 47 mm, Traversing path: 5 m, Traversing rate: 3 m/s
Flame resistance	in accordance with DIN UL-Style 20549
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
	-25 °C ... 90 °C (Plug / socket)

SAC-4P-10,0-100/M 8FS - Sensor/actuator cable



1577590

<https://www.phoenixcontact.com/us/products/1577590>

Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-4P-10,0-100/M 8FS - Sensor/actuator cable

1577590

<https://www.phoenixcontact.com/us/products/1577590>




Drawings

Dimensional drawing



Socket M8 x 1, straight

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side


SAC-4P-10,0-100/M 8FS - Sensor/actuator cable



1577590

<https://www.phoenixcontact.com/us/products/1577590>

Circuit diagram



Contact assignment of M8/M12 plugs/sockets

SAC-4P-10,0-100/M 8FS - Sensor/actuator cable



1577590

<https://www.phoenixcontact.com/us/products/1577590>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

SAC-4P-10,0-100/M 8FS - Sensor/actuator cable



1577590
<https://www.phoenixcontact.com/us/products/1577590>

Environmental product compliance

China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com