

# RC-12P1N8A7500 - Coupler connector



1597503

<https://www.phoenixcontact.com/us/products/1597503>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Coupler connector, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, coding: N, this item is expected to be lead-free from Q4 2025 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1597503
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFG
GTIN	4046356216432
Weight per piece (including packing)	83.15 g
Weight per piece (excluding packing)	79.24 g
Country of origin	DE

# RC-12P1N8A7500 - Coupler connector



1597503

<https://www.phoenixcontact.com/us/products/1597503>

## Technical data

### Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

### Product properties

Product type	Circular connector (cable-side)
Thread type	M23

### Material specifications

Flammability rating according to UL 94	V0
--	----

### Connector

#### Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Number Contact (Contact group 1)	12
Diameter Contact (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Type	Coupling housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	Pg9
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP65 IP67

# RC-12P1N8A7500 - Coupler connector



1597503

<https://www.phoenixcontact.com/us/products/1597503>

	IP68
--	------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Permissible humidity (storage/transport)	50 % ... 65 %


# RC-12P1N8A7500 - Coupler connector

1597503

<https://www.phoenixcontact.com/us/products/1597503>

## Drawings

Schematic diagram



Connector pin assignment


# RC-12P1N8A7500 - Coupler connector

1597503

<https://www.phoenixcontact.com/us/products/1597503>



Schematic diagram



Connector pin assignment

# RC-12P1N8A7500 - Coupler connector



1597503

<https://www.phoenixcontact.com/us/products/1597503>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-12P1N8A7500 - Coupler connector



1597503

<https://www.phoenixcontact.com/us/products/1597503>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	8f4b03d4-6759-4553-8e72-a56861030633

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)