

FLKM-PA-2D15/HW/DI/C300 - Front adapter



2901879
<https://www.phoenixcontact.com/us/products/2901879>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE front adapter, for Honeywell C300, Series C I/O. Specially designed for connecting PLC-V8/D15.../IN. Transmission of 2x 8 channels.

Your advantages

- Front adapter with two 15-pos. D-SUB connectors
- Connection of a maximum of 2x 8 digital outputs

Commercial data

Item number	2901879
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK231H
GTIN	4046356637053
Weight per piece (including packing)	100.3 g
Weight per piece (excluding packing)	100.3 g
Customs tariff number	85366990
Country of origin	DE

FLKM-PA-2D15/HW/DI/C300 - Front adapter



2901879

<https://www.phoenixcontact.com/us/products/2901879>

Technical data

Product properties

Product type	Front adapter
Product family	VARIOFACE

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Current (per branch)	≤ 1 A

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 μs)

Supported controller HONEYWELL Experion PKS C300/C-Series

Suitable I/O card	TDIL01 (non-redundant)
	TDIL11 (redundant)

Connection data

Connection 1 (control level)

Connection method	Plug-in connection
Number of connections	2
Number of positions	16
Pitch	5.08 mm

Connection 2 (field level)

Connection in acc. with standard	IEC 60807-2
Connection method	D-SUB pin strip
Screw thread	UNC 4-40
Number of connections	2
Number of positions	15
Insertion/withdrawal cycles	> 500
Pitch	2.74 mm

Connection 3 (shield)

Connection method	Spade connection
Number of positions	1
Note	2,8 x 0,8

FLKM-PA-2D15/HW/DI/C300 - Front adapter



2901879

<https://www.phoenixcontact.com/us/products/2901879>

Dimensions

Item dimensions

Width	93.8 mm
Height	28 mm
Depth	47.04 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	Plug-in mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKM-PA-2D15/HW/DI/C300 - Front adapter




2901879

<https://www.phoenixcontact.com/us/products/2901879>

Drawings

Circuit diagram



FLKM-PA-2D15/HW/DI/C300 connection scheme

FLKM-PA-2D15/HW/DI/C300 - Front adapter



2901879

<https://www.phoenixcontact.com/us/products/2901879>

Classifications

ECLASS

ECLASS-13.0	27242292
ECLASS-15.0	27242292

ETIM

ETIM 9.0	EC002584
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

FLKM-PA-2D15/HW/DI/C300 - Front adapter



2901879
<https://www.phoenixcontact.com/us/products/2901879>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com