


UC-EMLP (20X8) YE - Plastic label



0822631

<https://www.phoenixcontact.com/us/products/0822631>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plastic label, Sheet, yellow, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 10, text field height: 8 mm, text field width: 20 mm

Your advantages

- The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK printing system
- The UC-EMLP ... UniCard marking range includes self-adhesive device markers with good adhesive properties
- The sheets provide additional space for project information and function text that can be helpful during further assembly
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

Item number	0822631
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG10
Product key	BG2417
GTIN	4046356328593
Weight per piece (including packing)	8.3 g
Weight per piece (excluding packing)	8.3 g
Customs tariff number	39269097
Country of origin	PL

UC-EMLP (20X8) YE - Plastic label



0822631

<https://www.phoenixcontact.com/us/products/0822631>

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Marking

Number of individual labels	10
Number of individual labels per row	2
Identification technology	UV LED technology

Dimensions

Width	20.00 mm
Height	8.00 mm
Depth	1.30 mm

Material specifications

Adhesive strength	250 µm
Adhesive	Acrylic
Color	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V2
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

UC-EMLP (20X8) YE - Plastic label



0822631

<https://www.phoenixcontact.com/us/products/0822631>

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	1 Year

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

UC-EMLP (20X8) YE - Plastic label



0822631

<https://www.phoenixcontact.com/us/products/0822631>

Mounting

Mounting type	adhesive
---------------	----------

UC-EMLP (20X8) YE - Plastic label



0822631

<https://www.phoenixcontact.com/us/products/0822631>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UC-EMLP (20X8) YE - Plastic label



0822631
<https://www.phoenixcontact.com/us/products/0822631>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.162 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com