

CUC-IND-J1ST-S/R4LS-LED - Modular RJ45 PCB connectors



1091947
<https://www.phoenixcontact.com/us/products/1091947>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular RJ45 PCB connectors, design: THD, number of positions: 8 (8P8C), 10 Gbps, degree of protection: IP20, connection method: Female, Tray

Your advantages

- Ideal for demanding applications due to the high shock and vibration resistance as well as the extended temperature range
- 360° shielding ensures reliable transmission, even in industrial applications
- Housing shield springs enable an optimized EMC shielding concept
- With integrated hybrid LEDs as optical status indicators of data transmission
- Enables data transmission rates of up to 10 Gbps
- Automated handling process thanks to reflow capability
- The extended temperature range from -40°C to +105°C enables use in demanding industrial applications
- Tray packing

Commercial data

Item number	1091947
Packing unit	84 pc
Minimum order quantity	84 pc
Sales key	AB12
Product key	ABNADA
GTIN	4055626906362
Weight per piece (including packing)	5.36 g
Weight per piece (excluding packing)	5.3 g
Customs tariff number	85366930
Country of origin	CN

CUC-IND-J1ST-S/R4LS-LED - Modular RJ45 PCB connectors



1091947

<https://www.phoenixcontact.com/us/products/1091947>

Technical data

Product properties

Product type	Data connector (device side)
Sensor type	Universal
Number of positions	8
Note number of positions	8P8C
Connection profile	RJ45
Housing shield springs	No
Number of slots	1
Shielded	yes
LED	yes

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage	72 V DC
Rated surge voltage	1.5 kV DC
Rated current	1.5 A
Frequency range	10 Hz ... 500 Hz
Insulation resistance	> 500 MΩ
Transmission speed	10 Gbps
Transmission speed	10 Gbps
Power transmission	PoE++

Connection data

Connection technology

Connection method	Female
-------------------	--------

Signaling

Status display present	yes
------------------------	-----

Dimensions

Width	16.1 mm
Height	14.7 mm
Length	17.9 mm
Installed height	14.30 mm
Orientation to PCB	180.00 °
Data pin length	3.18 mm

Material specifications

Material Metal surface contact area (top layer)	Au (1.27 µm/50 µ")
---	--------------------

CUC-IND-J1ST-S/R4LS-LED - Modular RJ45 PCB connectors



1091947

<https://www.phoenixcontact.com/us/products/1091947>

Material Metal surface soldering area (top layer)	Au
Material Metal surface soldering area (middle layer)	Ni
Material Metal surface contact area (middle layer)	Ni
Material Housing	Copper alloy (Housing (shielding))
Material	PA (Housing (female/insert))
Material Contact	Copper alloy
Material	Metal

Cable/line

Test voltage Core/Core	1 kV DC
Test voltage Core/Shield	1.50 kV DC
Halogen-free	yes
Flame resistance	UL 94 V0

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 750
Insertion force	< 20 N
Withdrawal force	< 20 N

Environmental and real-life conditions

Test specification

Frequency	10-500 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm
Acceleration	50.00 m/s ²
Test duration	20.00 s

Test specification

Specification	IEC60068-2-27
Acceleration	295.00 m/s ²

Ambient conditions

Degree of protection (when plugged in)	IP20
Degree of protection (not plugged in)	IP20
Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 105 °C

Standards and regulations

Flame resistance	UL 94 V0
------------------	----------

Mounting

Processing notes

Moisture Sensitive Level	MSL 1
--------------------------	-------

CUC-IND-J1ST-S/R4LS-LED - Modular RJ45 PCB connectors



1091947

<https://www.phoenixcontact.com/us/products/1091947>

Classification temperature T _c	260 °C
Solder cycles in the reflow	3

Packaging specifications

Type of packaging	Tray
-------------------	------

CUC-IND-J1ST-S/R4LS-LED - Modular RJ45 PCB connectors




1091947

<https://www.phoenixcontact.com/us/products/1091947>

Drawings

Diagram



Classification wave soldering profile

CUC-IND-J1ST-S/R4LS-LED - Modular RJ45 PCB connectors



1091947

<https://www.phoenixcontact.com/us/products/1091947>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1091947>



cUL Recognized
Approval ID: FILE E 335024



UL Recognized
Approval ID: FILE E 335024

CUC-IND-J1ST-S/R4LS-LED - Modular RJ45 PCB connectors



1091947
<https://www.phoenixcontact.com/us/products/1091947>

Classifications

ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-IND-J1ST-S/R4LS-LED - Modular RJ45 PCB connectors



1091947

<https://www.phoenixcontact.com/us/products/1091947>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com