

CA-63S1N12HZ00X - Device connector rear mounting



1245473

<https://www.phoenixcontact.com/us/products/1245473>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector rear mounting, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 6+3, Direction of rotation: Standard, contact connection type: Socket, Solder connection, Axial seal, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires
- Application-specific panel mounting optionally with thread or anti-rotation protection and lock nut

Commercial data

Item number	1245473
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABRAER
GTIN	4063151413224
Weight per piece (including packing)	48.8 g
Weight per piece (excluding packing)	43.967 g
Country of origin	DE

CA-63S1N12HZ00X - Device connector rear mounting



1245473

<https://www.phoenixcontact.com/us/products/1245473>

Technical data

Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Insulating body

Coding	N
Material (Insulating body)	PA 6.6
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Socket
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	6+3
Number Contact (Contact group 1)	3
Diameter Contact (Contact group 1)	2 mm
Litz wire cross-section max. Contact (Contact group 1)	2.5 mm ²
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number Contact (Contact group 2)	16
Diameter Contact (Contact group 2)	1 mm
Litz wire cross-section max. Contact (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A

Housing

Type	Feed-through header
Thread type	M23
Design	straight
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Mounting type	Rear wall/screw mounting (M25 x 1,5)
Assembly note	Central fastening

CA-63S1N12HZ00X - Device connector rear mounting



1245473

<https://www.phoenixcontact.com/us/products/1245473>

Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67
Seal for the device	Axial seal


Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Drawings

Schematic diagram




Connector pin assignment

1245473

<https://www.phoenixcontact.com/us/products/1245473>

Schematic diagram




Connector pin assignment

1245473

<https://www.phoenixcontact.com/us/products/1245473>

Schematic diagram



Dimensional drawing

CA-63S1N12HZ00X - Device connector rear mounting



1245473

<https://www.phoenixcontact.com/us/products/1245473>

Classifications

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

CA-63S1N12HZ00X - Device connector rear mounting



1245473

<https://www.phoenixcontact.com/us/products/1245473>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com