

1402119

https://www.phoenixcontact.com/us/products/1402119

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M8, coding: A, on Socket straight M8, cable length: 0.6 m

Commercial data

Item number	1402119
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1BCA
GTIN	4046356584609
Weight per piece (including packing)	22.3 g
Weight per piece (excluding packing)	23.8 g
Country of origin	PL



1402119

https://www.phoenixcontact.com/us/products/1402119

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A
Insulation characteristics	
Overvoltage category	II .
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	НВ
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated
Outer sheath, material	PUR
Conductor material	Bare Cu litz wires

Electrical properties

Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	48 V AC
	60 V DC
Nominal current I _N	4 A
Max. conductor resistance	78 Ω/km

Mechanical properties

Mechanical data

Max. bending cycles 4000000	Max. bending cycles	4000000
-----------------------------	---------------------	---------

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Туре	Plug straight M8
Number of positions	3



1402119

https://www.phoenixcontact.com/us/products/1402119

Coding type	A
Connection 2	
Туре	Socket straight M8
Number of positions	3

Cable/line

	0.0
Cable length	0.6 m

PUR halogen-free black [PUR]

Dimensional drawing



Cable weight	23 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	4
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross section	4x 0.25 mm² (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.02 mm (Signal line)
External cable diameter	3.95 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation)
	approx. 0.50 mm (Outer cable sheath)
Overall twist	4 wires, twisted
Max. conductor resistance	max. 78 Ω /km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	20 mm
Smallest bending radius, movable installation	40 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 44 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 5 m/s ²



1402119

https://www.phoenixcontact.com/us/products/1402119

Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥2000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2
	DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents
	hydrolysis and microbe resistant
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable
	Silicone-free
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C 80 °C (cable, fixed installation)
	-25 °C 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C 90 °C (Plug / socket)
	-40 °C 80 °C (cable, fixed installation)
	-5 °C 80 °C (Cable, flexible installation)




1402119

https://www.phoenixcontact.com/us/products/1402119


Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Dimensional drawing




Socket M8 x 1, straight



1402119


https://www.phoenixcontact.com/us/products/1402119

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side



1402119

https://www.phoenixcontact.com/us/products/1402119

Classifications

ECLASS

	ECLASS-13.0	27060311	
	ECLASS-15.0	27060311	
ETIM			
	ETIM 9.0	EC001855	
UNSPSC			
	UNSPSC 21.0	26121600	



1402119

https://www.phoenixcontact.com/us/products/1402119

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions		
China RoHS			
Environment friendly use period (EFUP)	EFUP-E		
	No hazardous substances above the limits		
EU REACH SVHC			
REACH candidate substance (CAS No.)	No substance above 0.1 wt%		

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com