

SAC-2P-M12MS/15,0-915/M12FS - Bus system cable



1404625

<https://www.phoenixcontact.com/us/products/1404625>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, PROFIBUS, 2-position, PUR/PVC, blue, shielded, Plug straight M12, coding: B, on Socket straight M12, coding: B, cable length: 15 m

Commercial data

Item number	1404625
Packing unit	1 pc
Minimum order quantity	25 pc
Note	Made to order (non-returnable)
Product key	AF1CJC
GTIN	4046356704731
Weight per piece (including packing)	1,155.1 g
Weight per piece (excluding packing)	1,155.1 g
Country of origin	PL

SAC-2P-M12MS/15,0-915/M12FS - Bus system cable



1404625

<https://www.phoenixcontact.com/us/products/1404625>

Technical data

Product properties

Product type	Data cable preassembled
Application	Bus system
Sensor type	PROFIBUS
Number of positions	2
No. of cable outlets	1
Shielded	yes
Coding	B

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Interfaces

Bus system	PROFIBUS
Signal type/category	PROFIBUS

Signaling

Status display	no
Status display present	no

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A
Transmission medium	Copper

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR

SAC-2P-M12MS/15,0-915/M12FS - Bus system cable



1404625

<https://www.phoenixcontact.com/us/products/1404625>

Connection assignment

Contact Color (signal designation) Contact (optional)	2 (Plug) GN (A cable) 2 (Socket)
	4 (Plug) RD (B cable) 4 (Socket)

Connector

Connection 1

Type	Plug straight M12
Number of positions	2
Coding type	B (inverse)

Connection 2

Type	Socket straight M12
Number of positions	2
Coding type	B

Cable/line

Cable length	15 m
--------------	------

PROFIBUS [915]

Cable weight	74 kg/km
Number of positions	2
Shielded	yes
Cable type	PROFIBUS [915]
Conductor structure	1x2xAWG24/19
Conductor structure signal line	19x 0.14 mm
AWG signal line	24
Conductor cross section	2x 0.25 mm ²
Wire diameter incl. insulation	2.56 mm
External cable diameter	8.00 mm ±0.4 mm
Outer sheath, material	PUR
External sheath, color	blue
Conductor material	Bare Cu litz wires
Material wire insulation	Foamed PE
Single wire, color	red, green
Thickness, outer sheath	approx. 0.80 mm
Overall twist	2 wires, twisted
Optical shield covering	70 %

SAC-2P-M12MS/15,0-915/M12FS - Bus system cable



1404625

<https://www.phoenixcontact.com/us/products/1404625>

	Acceleration: 4 m/s ²
Tensile strength	≤ 100 N
Flame resistance	according to IEC 60332-1
Resistance to oil	Resistant to mineral oils and grease
Ambient temperature (operation)	-40 °C ... 80 °C (Cable, flexible installation)


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)


Drawings

Dimensional drawing




Plug, M12 x 1, straight, shielded

Dimensional drawing



M12 x 1 socket, straight, shielded

Schematic diagram




Pin assignment M12 male connector, 5-pos., B-coded, male side

1404625


<https://www.phoenixcontact.com/us/products/1404625>

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side

Circuit diagram



SAC-2P-M12MS/15,0-915/M12FS - Bus system cable



1404625

<https://www.phoenixcontact.com/us/products/1404625>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1404625>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

SAC-2P-M12MS/15,0-915/M12FS - Bus system cable



1404625

<https://www.phoenixcontact.com/us/products/1404625>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-2P-M12MS/15,0-915/M12FS - Bus system cable



1404625

<https://www.phoenixcontact.com/us/products/1404625>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	13.055 kg CO2e
---------	----------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com