

ST-08P1N8ACK04S - Front panel feed-through



1617932

<https://www.phoenixcontact.com/us/products/1617932>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Front panel feed-through, straight, SPEEDCON, M17, number of positions: 8, contact connection type: Pin, Flat gasket, shielded: yes, flange dimensions: 25.75 mm x 25.75 mm, cable diameter range: 9 mm ... 11 mm, number of positions: 8, connection method: Crimp connection, series: ST

Your advantages

- Reduced size: ideal for compact devices
- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly
- Flexible use: reliably connect various cable diameters
- User-specific, suitable for front and rear mounting

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1617932 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB31 |
| Product key | ABRADJ |
| GTIN | 4046356708906 |
| Weight per piece (including packing) | 43.8 g |
| Weight per piece (excluding packing) | 42.624 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

Technical data

Notes

| | |
|--------------------|---|
| Order information: | Order crimp contacts Ø 1 mm separately |
| Safety note | |
| Safety note | <p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none"> • WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible. • WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product. • The products are suitable for applications in plant, controller, and electrical device engineering. • When operating the connectors in outdoor applications, they must be separately protected against environmental influences. • Assembled products may not be manipulated or improperly opened. • Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products). • When using the product in direct connection with third-party manufacturers, the user is responsible. • For operating voltages > 50 V AC, conductive connector housings must be grounded • Ensure that the protective or functional ground has been properly connected. • VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector • Only use tools recommended by Phoenix Contact • The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product. • Operate the connector only when it is fully plugged in and interlocked. • Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards. • Observe the minimum bending radius of the cable. Lay the cable without twisting it. • The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting |

ST-08P1N8ACK04S - Front panel feed-through



1617932

<https://www.phoenixcontact.com/us/products/1617932>

warnings (e.g. DIN EN ISO 13732-1:2008-12).

Mounting

| | |
|---------------|-----------------------------------|
| Mounting type | Front/rear mounting (4x Ø 3.2 mm) |
|---------------|-----------------------------------|

Product properties

| | |
|---------------------|-----------------------------------|
| Product type | Circular connectors (device side) |
| Series | ST |
| Application | Signal |
| Number of positions | 8 |
| Connection profile | 8 |
| Shielded | yes |
| Coding | N |
| Thread type | M17 |

Dimensions

Housing

| | |
|-------------------|---------------------|
| Flange dimensions | 25.75 mm x 25.75 mm |
|-------------------|---------------------|

Material specifications

| | |
|------------------|-------|
| Material Housing | Metal |
| Seal material | FPM |

Electrical properties

Contact: Contact group 1

| | |
|-----------------------|---------|
| Contact diameter | 1 mm |
| Nominal current I_N | 8 A |
| Nominal voltage U_N | 48 V AC |
| | 74 V DC |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Rated surge voltage | 1.5 kV |

Connection data

Conductor connection

| | |
|-------------------------|------------------|
| Connection method | Crimp connection |
| Contact connection type | Pin |

Connector

| | |
|-----------------------|----------|
| Type | straight |
| Direction of rotation | Standard |

Cable/line

| | |
|-------------------------|----------------|
| External cable diameter | 9 mm ... 11 mm |
|-------------------------|----------------|

ST-08P1N8ACK04S - Front panel feed-through



1617932

<https://www.phoenixcontact.com/us/products/1617932>

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Altitude | 3000 m |

ST-08P1N8ACK04S - Front panel feed-through




1617932

<https://www.phoenixcontact.com/us/products/1617932>


Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Installation dimensions


ST-08P1N8ACK04S - Front panel feed-through

1617932

<https://www.phoenixcontact.com/us/products/1617932>




Schematic diagram



Installation dimensions

Schematic diagram




Connector pin assignment

ST-08P1N8ACK04S - Front panel feed-through



1617932

<https://www.phoenixcontact.com/us/products/1617932>



I = current strength, ϑ = ambient temperature, 8x 8 A

ST-08P1N8ACK04S - Front panel feed-through





1617932


<https://www.phoenixcontact.com/us/products/1617932>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1617932>

|  cUL Recognized Approval ID: E335019-20111129 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 48 V | 5 A | - | - |

|  UL Recognized Approval ID: E335019-20111129 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 48 V | 5 A | - | - |

|  UL Recognized Approval ID: E153698-20140124 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 48 V | 5 A | - | - |

|  cUL Recognized Approval ID: E153698-20140124 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 48 V | 5 A | - | - |

ST-08P1N8ACK04S - Front panel feed-through



1617932

<https://www.phoenixcontact.com/us/products/1617932>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440109 |
| ECLASS-15.0 | 27440109 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC003569 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

ST-08P1N8ACK04S - Front panel feed-through



1617932
<https://www.phoenixcontact.com/us/products/1617932>

Environmental product compliance

| | |
|---|---|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 85f44db6-72de-4b2d-9727-a442d14f6b23 |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com