

# EV-T2G3PC-3AC20A-4,0M2,5ESBK01 - AC charging cable



1623508

<https://www.phoenixcontact.com/us/products/1623508>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect comfort, Type 2, Mobile AC charging cable, 20 A permanent, 480 V AC, with vehicle charging connector and infrastructure charging plug, cable: 4 m, black, straight, with protective cap, housing: black, gray, PHOENIX CONTACT logo, IEC 62196-2, for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets

## Product description

Mobile AC charging cable with vehicle charging connector and infrastructure charging plug for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets, compatible with type 2 infrastructure charging sockets at charging stations for e-mobility (EVSE)

## Your advantages

- Complete product range
- Convenient handling due to the ergonomic, triple award-winning design
- Available with your logo on request - for consistent branding of your charging station
- Longitudinal water tightness reliably prevents water ingress
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Tested in accordance with automotive standards LV124, LV214, and LV215-2
- Tested in accordance with EV Ready 37 requirements
- Laser-marked mating face in accordance with DIN EN 17186

## Commercial data

Item number	1623508
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	XWBEBEC
GTIN	4055626177892
Weight per piece (including packing)	1,658 g
Weight per piece (excluding packing)	1,737 g
Country of origin	PL



# EV-T2G3PC-3AC20A-4,0M2,5ESBK01 - AC charging cable



1623508

<https://www.phoenixcontact.com/us/products/1623508>

## Technical data

### Product properties

Product type	AC charging cable
Product family	CHARX connect comfort
Application	for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets compatible with type 2 infrastructure charging sockets at charging stations for electromobility (EVSE)
Design	with protective cap
Charging standard	Type 2
Charging mode	Mode 3, Case B
Affixed logo	PHOENIX CONTACT logo
Customer variations	On request

### Electrical properties

#### Charging power and current (AC charging (3-phase))

Type of charging current	AC 3-phase
Charging current	20 A AC (3-phase)
Charging power	16.63 kW (3-phase)
Rated voltage	480 V

#### Pin assignment (Leistungskontakte)

Note on the connection method	Crimp connection, cannot be disconnected
Number	5 (L1, L2, L3, N, PE)
Rated voltage	480 V AC
Rated current	20 A

#### Pin assignment (Signalkontakte)

Note on the connection method	Crimp connection, cannot be disconnected
Type of signal transmission	Pulse width modulation
Number	2 (CP, PP)
Rated voltage	30 V AC
Rated current	2 A
Coding	680 $\Omega$ (between PE and PP)

## Dimensions

### Infrastructure charging plug

Dimensional drawing	
---------------------	--



# EV-T2G3PC-3AC20A-4,0M2,5ESBK01 - AC charging cable




1623508

<https://www.phoenixcontact.com/us/products/1623508>

	Infrastructure plug
Width	58 mm
Height	131.8 mm
Depth	215.9 mm

## Vehicle charging connector

Dimensional drawing	
	Vehicle connector
Width	70 mm
Height	137 mm
Depth	215.9 mm

## Material specifications

Color (Housing)	black (9005)
Color (Handle area)	gray (7042)
Color (Mating face)	black (9005)
Color (Protective cap)	black (9005)
Color (Cable)	black (9005)
Material (Vehicle charging connector)	Plastic
Material (Infrastructure charging plug)	Plastic
Material (Cable outer sheath)	TPE-U
Material (Contact surface)	Silver
Note	The color appearance and gloss level of the charging cable may vary.

## Cable/line

Cable length	4 m
Wiring standards/regulations	prEN 50620/DIN EN 50620
Wiring certifications	VDE
Cable weight	max. 250.00 kg/km
Cable type	Class 5
Cable type	straight
Cable structure	5 x 1.5 mm <sup>2</sup> + 1 x 0.5 mm <sup>2</sup>
External cable diameter	11.60 mm ±0.3 mm
Outer sheath, material	TPE-U
Cable resistance	≤ 0.00798 Ω/m (based on a power core, at an ambient temperature of 20°C)
Bending radius	min. 192 mm (15x diameter)



# EV-T2G3PC-3AC20A-4,0M2,5ESBK01 - AC charging cable



1623508

<https://www.phoenixcontact.com/us/products/1623508>

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 10000
Insertion force	< 100 N
Withdrawal force	< 100 N

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (Vehicle charging connector)	IP44 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
Degree of protection (Infrastructure charging plug)	IP44 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
Degree of protection (Protective cap)	IP54
Ambient temperature (operation)	-40 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	5000 m (above sea level)

## Standards and regulations

### Standards

Standards/regulations	IEC 62196-2
-----------------------	-------------



# EV-T2G3PC-3AC20A-4,0M2,5ESBK01 - AC charging cable




1623508

<https://www.phoenixcontact.com/us/products/1623508>


## Drawings

Dimensional drawing



## Vehicle connector

Dimensional drawing



## Infrastructure plug




# EV-T2G3PC-3AC20A-4,0M2,5ESBK01 - AC charging cable

1623508

<https://www.phoenixcontact.com/us/products/1623508>

Connection diagram



Pin assignment of Infrastructure Plug



# EV-T2G3PC-3AC20A-4,0M2,5ESBK01 - AC charging cable


1623508

<https://www.phoenixcontact.com/us/products/1623508>


Schematic diagram




[I]



[II]



[III]



[IV]



[V]

Operating instructions




# EV-T2G3PC-3AC20A-4,0M2,5ESBK01 - AC charging cable



1623508


<https://www.phoenixcontact.com/us/products/1623508>

Schematic diagram



Pin assignment of the Vehicle Connector

Schematic diagram




Terminology definition




1623508  
<https://www.phoenixcontact.com/us/products/1623508>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1623508>

	<b>IECEE CB Scheme</b> Approval ID: DE1-65890			
	Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
	keine			
	480 V	20 A	-	-

	<b>VDE approval of drawings</b> Approval ID: 40045394			
	Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
	keine			
	480 V	20 A	-	-



1623508  
<https://www.phoenixcontact.com/us/products/1623508>

Classifications

ECLASS

ECLASS-13.0	27144705
ECLASS-15.0	27144705

ETIM

ETIM 9.0	EC002897
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------



# EV-T2G3PC-3AC20A-4,0M2,5ESBK01 - AC charging cable



1623508

<https://www.phoenixcontact.com/us/products/1623508>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f07faaf7-608a-44fd-a371-6f767797edee

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)