

# UKK 3-MSTB-5,08 - Double-level terminal block



2770888

<https://www.phoenixcontact.com/us/products/2770888>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Double-level terminal block, Current and voltage are determined by the plug used., nom. voltage: 250 V, nominal current: 10 A, connection method: Screw/plug-in connection, 1st and 2nd level connection left, cross section: 0.2 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, NS 32, color: gray

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2770888       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE12          |
| Product key                          | BE1241        |
| GTIN                                 | 4017918068110 |
| Weight per piece (including packing) | 8.502 g       |
| Weight per piece (excluding packing) | 8.177 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | TR            |

# UKK 3-MSTB-5,08 - Double-level terminal block



2770888

<https://www.phoenixcontact.com/us/products/2770888>

## Technical data

### Notes

|         |                                                      |
|---------|------------------------------------------------------|
| General | Current and voltage are determined by the plug used. |
|---------|------------------------------------------------------|

### Product properties

|                       |                            |
|-----------------------|----------------------------|
| Product type          | Multi-level terminal block |
| Product family        | UK                         |
| Number of positions   | 1                          |
| Pitch                 | 5.08 mm                    |
| Number of connections | 4                          |
| Number of rows        | 2                          |
| Potentials            | 2                          |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                                                 |      |
|-------------------------------------------------|------|
| Rated surge voltage                             | 4 kV |
| Maximum power dissipation for nominal condition | 0 W  |

### Connection data

#### 1st and 2nd level connection left

|                                                                                                                   |                                              |
|-------------------------------------------------------------------------------------------------------------------|----------------------------------------------|
| Connection method                                                                                                 | Screw/plug-in connection                     |
| Screw thread                                                                                                      | M3                                           |
| Tightening torque                                                                                                 | 0.5 ... 0.6 Nm                               |
| Stripping length                                                                                                  | 8 mm                                         |
| Internal cylindrical gage                                                                                         | A3                                           |
| Conductor cross-section rigid                                                                                     | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>    |
| Cross section AWG                                                                                                 | 24 ... 12 (converted acc. to IEC)            |
| Conductor cross-section flexible                                                                                  | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Conductor cross-section, flexible [AWG]                                                                           | 24 ... 14 (converted acc. to IEC)            |
| Conductor cross-section flexible (ferrule without plastic sleeve)                                                 | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)                                                    | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section flexible (2 conductors with the same cross-section, with TWIN ferrule and plastic sleeve) | 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup>    |
| 2 conductors with same cross section, solid                                                                       | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, flexible                                                                    | 0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup>    |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve                               | 0.25 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve                         | 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup>    |
| Nominal current                                                                                                   | 10 A                                         |

# UKK 3-MSTB-5,08 - Double-level terminal block




2770888

<https://www.phoenixcontact.com/us/products/2770888>

|                      |                                                       |
|----------------------|-------------------------------------------------------|
| Maximum load current | 12 A (with 4 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage      | 250 V                                                 |

## Dimensions

|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 5.08 mm                                                                            |
| End cover width     | 2.5 mm                                                                             |
| Height              | 50 mm                                                                              |
| Depth on NS 35/7,5  | 53.5 mm                                                                            |
| Pitch               | 5.08 mm                                                                            |

## Material specifications

|                                                                         |                 |
|-------------------------------------------------------------------------|-----------------|
| Color                                                                   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V2              |
| Insulating material group                                               | I               |
| Insulating material                                                     | PA              |
| Static insulating material application in cold                          | -40 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 125 °C          |

## Electrical tests

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 2.21 kV     |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|               |                                                |
|---------------|------------------------------------------------|
| Specification | DIN EN 50155 (VDE 0115-200):2018-05            |
| Spectrum      | Long life test category 2, bogie-mounted       |
| Frequency     | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |

# UKK 3-MSTB-5,08 - Double-level terminal block



2770888

<https://www.phoenixcontact.com/us/products/2770888>

|                        |                                           |
|------------------------|-------------------------------------------|
| ASD level              | 6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz |
| Acceleration           | 3.12g                                     |
| Test duration per axis | 5 h                                       |
| Test directions        | X-, Y- and Z-axis                         |
| Result                 | Test passed                               |

## Shocks

|                                |                                   |
|--------------------------------|-----------------------------------|
| Pulse shape                    | Half-sine                         |
| Acceleration                   | 30g                               |
| Shock duration                 | 18 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |
| Result                         | Test passed                       |

## Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C (max. operating temperature see derating curve)                    |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (operation)         | 20 % ... 90 %                                                             |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |
|               | NS 32     |


# UKK 3-MSTB-5,08 - Double-level terminal block

2770888

<https://www.phoenixcontact.com/us/products/2770888>



## Drawings



# UKK 3-MSTB-5,08 - Double-level terminal block



2770888

<https://www.phoenixcontact.com/us/products/2770888>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2770888>

|  <b>CSA</b><br>Approval ID: 13631 |                                |                                |                   |                               |
|--------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|                                                                                                                    | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                              |                                |                                |                   |                               |
|                                                                                                                    | 300 V                          | 10 A                           | 28 - 12           | -                             |

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                                |                                |                   |                               |
|----------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|                                                                                                                                  | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| B                                                                                                                                |                                |                                |                   |                               |
|                                                                                                                                  | 300 V                          | 10 A                           | 30 - 12           | -                             |
| F                                                                                                                                |                                |                                |                   |                               |
|                                                                                                                                  | 250 V                          | 10 A                           | 30 - 12           | -                             |
| D                                                                                                                                |                                |                                |                   |                               |
|                                                                                                                                  | 300 V                          | 10 A                           | 30 - 12           | -                             |

# UKK 3-MSTB-5,08 - Double-level terminal block



2770888

<https://www.phoenixcontact.com/us/products/2770888>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250102 |
| ECLASS-15.0 | 27250102 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UKK 3-MSTB-5,08 - Double-level terminal block



2770888

<https://www.phoenixcontact.com/us/products/2770888>

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 996774be-3753-40da-a58c-34de067a70d5 |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)