

PLC-BSC- 5DC/21 - Relay base



2980225

<https://www.phoenixcontact.com/us/products/2980225>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



6.2 mm PLC basic terminal block with screw connection, without relay or solid-state relay, for mounting on DIN rail NS 35/7,5, 1 changeover contact, input voltage 5 V DC

Commercial data

Item number	2980225
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C461
Product key	DK6221
GTIN	4017918820756
Weight per piece (including packing)	34.89 g
Weight per piece (excluding packing)	28.49 g
Customs tariff number	85366990
Country of origin	DE

PLC-BSC- 5DC/21 - Relay base



2980225

<https://www.phoenixcontact.com/us/products/2980225>

Technical data

Product properties

Product type	Relay socket
Product family	PLC-INTERFACE
Application	Universal
Operating mode	100% operating factor

Insulation characteristics

Pollution degree	3
------------------	---

Electrical properties

Protective circuit	Damping diode, polarity protection diode
--------------------	--

Input data

Nominal input voltage U_N	5 V DC
	The nominal voltage of the plug-on electromechanical relay or solid-state relay (see necessary accessories) deviates from the nominal input voltage of the base with integrated upstream circuit
Protective circuit	Freewheeling diode
Nominal input voltage U_N	5 V DC
	The nominal voltage of the plug-on electromechanical relay or solid-state relay (see necessary accessories) deviates from the nominal input voltage of the base with integrated upstream circuit

Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
	0.2 mm ² ... 2.5 mm ² (Single ferrule)
	2x 0.5 mm ² ... 1.5 mm ² (TWIN ferrule)
Conductor cross-section AWG	26 ... 14
Tightening torque	0.6 Nm ... 0.8 Nm

Signaling

Status display	LED
----------------	-----

Dimensions

Width	6.2 mm
Height	80 mm
Depth	94 mm

Material specifications

Color	gray (RAL 7042)
-------	-----------------

PLC-BSC- 5DC/21 - Relay base



2980225

<https://www.phoenixcontact.com/us/products/2980225>

Flammability rating according to UL 94 (Housing)
--

V0 (Housing)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)

-25 °C ... 60 °C

Ambient temperature (storage/transport)

-40 °C ... 85 °C

Approvals

CE

Certificate

CE-compliant

UKCA

Certificate

UKCA-compliant

Shipbuilding approval

Certificate

TAE0000196

Corrosive gas test

Identification

ISA-S71.04. G3 Harsh Group

EN 60068-2-60

Shipbuilding data

Temperature

D

Humidity

A

Vibration

B/C

EMC

B

Enclosure

Required protection according to the Rules shall be provided upon installation on board

EMC data

Electromagnetic compatibility

Conformance with EMC directive

Low Voltage Directive

Conformance with Low Voltage Directive
--

Standards and regulations

Standards/regulations

IEC/EN 60664-1

Mounting

Mounting type

DIN rail mounting

Assembly note

in rows with zero spacing

Mounting position

any

PLC-BSC- 5DC/21 - Relay base



2980225

<https://www.phoenixcontact.com/us/products/2980225>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2980225>



cUL Recognized
Approval ID: E238705



UL Recognized
Approval ID: E238705



EAC
Approval ID: RU D-DE.B*00573/18



DNV GL
Approval ID: TAE0000196

PLC-BSC- 5DC/21 - Relay base



2980225

<https://www.phoenixcontact.com/us/products/2980225>

Classifications

ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

ETIM

ETIM 9.0	EC001456
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
SCIP	6264205e-185d-4e61-ba3a-dea844d84847