

PTRV 8 BU/WHRD - Marshalling panel



3270134

<https://www.phoenixcontact.com/us/products/3270134>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marshalling panel, nom. voltage: 250 V, nominal current: 8 A, connection method: Push-in connection, 1st, 2nd, 3rd, 4th, 5th, 6th, 7th and 8th level, Rated cross section: 1.5 mm^2 , cross section: 0.14 mm^2 - 2.5 mm^2 , mounting: NS 35/7,5, NS 35/15, color: blue, color of connection elements: white, red

Your advantages

- Blue version for using in intrinsically safe circuits in potentially explosive areas (type of protection Ex i)
- High contact quality thanks to push-in technology as a replacement for Wire-Wrap®, TERMI-POINT®, etc.
- Individual color assignment of cable and terminal point to ensure error-free, safe operation
- Tool-free wiring in a confined space thanks to compact size
- The 2.3 mm test pick-off enables testing between the conductors with commercially available test probes

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3270134 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE62 |
| Product key | BE6211 |
| GTIN | 4055626046686 |
| Weight per piece (including packing) | 37.42 g |
| Weight per piece (excluding packing) | 37 g |
| Customs tariff number | 85369010 |
| Country of origin | PL |

PTRV 8 BU/WHRD - Marshalling panel



3270134

<https://www.phoenixcontact.com/us/products/3270134>

Technical data

Product properties

| | |
|-----------------------|----------------------|
| Product type | Marshalling terminal |
| Number of positions | 2 |
| Number of connections | 32 |
| Number of rows | 8 |
| Potentials | 8 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
|----------------------|-----|

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 4 kV |
| Maximum power dissipation for nominal condition | 0.56 W |

Connection data

| | |
|---------------------------------|---------------------|
| Number of connections per level | 4 |
| Nominal cross section | 1.5 mm ² |

1st, 2nd, 3rd, 4th, 5th, 6th, 7th and 8th level

| | |
|---|--|
| Connection method | Push-in connection |
| Stripping length | 8 mm ... 10 mm |
| Connection in acc. with standard | IEC 60947-7-1 |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Cross section AWG | 26 ... 14 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.14 mm ² ... 1.5 mm ² |
| Conductor cross-section, flexible [AWG] | 26 ... 16 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm ² ... 1.5 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.14 mm ² ... 1.5 mm ² |
| Nominal current | 8 A |
| Maximum load current | 8 A (with 1.5 mm ² conductor cross-section) |
| Nominal voltage | 250 V |
| Nominal cross section | 1.5 mm ² |

1st, 2nd, 3rd, 4th, 5th, 6th, 7th and 8th level Connection cross sections directly pluggable

| | |
|---|--|
| Conductor cross-section rigid | 0.34 mm ² ... 2.5 mm ² |
| Conductor cross-section, rigid [AWG] | 20 ... 14 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.34 mm ² ... 1.5 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.34 mm ² ... 1.5 mm ² |

Dimensions

| | |
|--------------------|---------|
| Width | 8.3 mm |
| Height | 100 mm |
| Depth on NS 35/7,5 | 87.5 mm |

PTRV 8 BU/WHRD - Marshalling panel



3270134

<https://www.phoenixcontact.com/us/products/3270134>

| | |
|-------------------|-------|
| Depth on NS 35/15 | 95 mm |
|-------------------|-------|

Material specifications

| | |
|---|-----------------|
| Color | blue (RAL 5015) |
| Color of connection elements | white (4x top) |
| | red (4x bottom) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 28 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Mechanical properties

Mechanical data

| | |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations


| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

Drawings

Circuit diagram



PTRV 8 BU/WHRD - Marshalling panel



3270134

<https://www.phoenixcontact.com/us/products/3270134>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3270134>

| CSA Approval ID: 2030668 | | | | |
|------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | 300 V | 10 A | 26 - 14 | - |
| D | 300 V | 10 A | 26 - 14 | - |

| IECEE CB Scheme Approval ID: NL-58817 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | 250 V | 8 A | - | - |

| | | | | |
|---|--|--|--|--|
| EAC Approval ID: RU C-DE.BL08.B.00682 | | | | |
|---|--|--|--|--|

| cULus Recognized Approval ID: E60425 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| D | 300 V | 10 A | 26 - 14 | - |

| KEMA-KEUR Approval ID: 71-102890 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| Only flexible conductors | 250 V | 8 A | - | 0.14 - 1.5 |
| Only rigid conductors | 250 V | 8 A | - | 0.14 - 2.5 |

| | | | | |
|---------------------------------------|--|--|--|--|
| DNV Approval ID: TAE000016Y | | | | |
|---------------------------------------|--|--|--|--|

PTRV 8 BU/WHRD - Marshalling panel



3270134

<https://www.phoenixcontact.com/us/products/3270134>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250105 |
| ECLASS-15.0 | 27250105 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

PTRV 8 BU/WHRD - Marshalling panel



3270134

<https://www.phoenixcontact.com/us/products/3270134>

Environmental product compliance

| | |
|---|--|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com