

RAD-ISM-5000-ANT-PAR-22-N - Antenna



5606174
<https://www.phoenixcontact.com/us/products/5606174>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Directional antenna, 5 GHz, gain: 22 dBi, polarization: linear, opening angle: h/v 12°/12°, degree of protection: IP55, connection: N (female), incl. mounting bracket and mast clips

Your advantages

- For large distances
- For point-to-point connections

Commercial data

Item number	5606174
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNC6A5
GTIN	4046356482080
Weight per piece (including packing)	7,783.65 g
Weight per piece (excluding packing)	7,783.65 g
Customs tariff number	85177000
Country of origin	US

Technical data

Product properties

Product type	Antenna
Gain	22 dBi
Vertical beamwidth	12 °
Horizontal beamwidth	12 °
Polarization	Linear vertical

Electrical properties

Frequency band	5 GHz
Frequency range	5.25 GHz ... 5.85 GHz
Impedance	50 Ω
Voltage standing wave ratio VSWR in a 50 Ω system	≤ 1.50

Connection data

Connection technology

Connection method	N (female)
Outside diameter	50 mm ... 114 mm (Mast)

Dimensions

Diameter	304.8 mm
----------	----------

External dimensions

Outside diameter	50 mm ... 114 mm (Mast)
------------------	-------------------------

Material specifications

Material	V2A
	V2A

Cable/line

Connecting cable	no
------------------	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP55
Ambient temperature (operation)	-40 °C ... 70 °C
Wind velocity	15.4321 km/h

Mounting

Mounting type	Mast mounting
---------------	---------------

Environmental product compliance

China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com