

WMTB HF (55X15)R RD CUS - Cable marker



8191198

<https://www.phoenixcontact.com/us/products/8191198>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, can be ordered: by line, red, labeled according to customer specifications, mounting type: Assembly with cable ties, cable diameter: ≥ 6 mm, text field height: 15 mm, text field width: 55 mm

Your advantages

- The WMTB HF ... conductor and cable marking is used for the identification and bundling conductors and cables indoors and outdoors
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The markers are made of a halogen-free material
- The highly flexible material adapts to the conductors and cables
- The marker has two fastening eyes so that it can be attached to the conductor by means of WT cable binders

Commercial data

Item number	8191198
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8131
GTIN	4055626024295
Weight per piece (including packing)	1.32 g
Weight per piece (excluding packing)	1.56 g
Country of origin	PL

WMTB HF (55X15)R RD CUS - Cable marker



8191198

<https://www.phoenixcontact.com/us/products/8191198>

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels per row	1
-------------------------------------	---

Dimensions

Width	15 mm
Length	55 mm

Material specifications

RoHS compliant	yes
Color	red (RAL 3001)
Material	PUR
Flammability rating according to UL 94	V2 (0,75 mm Wandstärke)
Components	halogen-free

Cable/line

External cable diameter	≥ 6.00 mm
-------------------------	-----------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

Wipe resistance of inscriptions

WMTB HF (55X15)R RD CUS - Cable marker



8191198

<https://www.phoenixcontact.com/us/products/8191198>

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-25 °C ... 100 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	10 °C ... 25 °C
Recommended humidity (storage/transport)	45 % ... 55 %
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

WMTB HF (55X15)R RD CUS - Cable marker



8191198

<https://www.phoenixcontact.com/us/products/8191198>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

WMTB HF (55X15)R RD CUS - Cable marker



8191198

<https://www.phoenixcontact.com/us/products/8191198>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com