

ESL 15X5 CUS - Insert strip

0824396

<https://www.phoenixcontact.com/us/products/0824396>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insert strip, can be ordered: in sheets, white, labeled according to customer specifications, mounting type: insert

Commercial data

Item number	0824396
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8144
GTIN	4046356352673
Weight per piece (including packing)	9 g
Weight per piece (excluding packing)	9 g
Country of origin	DE

ESL 15X5 CUS - Insert strip



0824396

<https://www.phoenixcontact.com/us/products/0824396>

Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Klemmenmarker
--------------	---------------

Marking

Identification technology	Plotter
---------------------------	---------

Dimensions

Width	5 mm
Length	15 mm

Material specifications

Foil strength	135 µm
Color	white
Material	Polyester foil
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	DIN EN ISO 1518-1:2011 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

ESL 15X5 CUS - Insert strip



0824396

<https://www.phoenixcontact.com/us/products/0824396>

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	insert
---------------	--------

ESL 15X5 CUS - Insert strip

0824396

<https://www.phoenixcontact.com/us/products/0824396>



Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

ESL 15X5 CUS - Insert strip



0824396

<https://www.phoenixcontact.com/us/products/0824396>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com