

RAD-PIG-EF316-N-RSMA - Antenna cable



2701402

<https://www.phoenixcontact.com/us/products/2701402>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Antenna cable for control cabinet feed-through, outside diameter: 3.2 mm (0.126 in.), inner conductor: stranded, attenuation: 0.6 / 0.9 / 1.4 dB at 0.9 / 2.4 / 5.8 GHz, connection: N (female) -> RSMA (male), cable length: 0.5 m (1.6 ft.)



Your advantages

- Halogen-free
- Flame-retardant
- UV resistant
- Oil-resistant
- For outdoor installation

Commercial data

Item number	2701402
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN23
Product key	DNN2Z2
GTIN	4046356746816
Weight per piece (including packing)	55 g
Weight per piece (excluding packing)	52.7 g
Customs tariff number	85442000
Country of origin	PL

RAD-PIG-EF316-N-RSMA - Antenna cable



2701402

<https://www.phoenixcontact.com/us/products/2701402>

Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type

Coaxial cable

Electrical properties

Frequency range

0.3 GHz ... 6 GHz

Impedance

50 Ω

Connection data

Connector connection

Connection method

RSMA (male)


Connector connection

Connection method

N (female)

Dimensions

Dimensional drawing



Hole diameter

16.1 mm

Material specifications

Outer sheath, material

RADOX®(LSFH)

Cable/line

Cable length

0.5 m

Cable type

EF 316

External cable diameter

2.50 mm

Outer sheath, material

RADOX®(LSFH)

External sheath, color

blue

Bending radius, long-term

12.50 mm

868 / 900 MHz

~ 0.6 dB (Attenuation of entire cable)

2.4 GHz

~ 0.9 dB (Attenuation of entire cable)

RAD-PIG-EF316-N-RSMA - Antenna cable



2701402

<https://www.phoenixcontact.com/us/products/2701402>

5.8 GHz	~ 1.4 dB (Attenuation of entire cable)
Resistance to oil	very good oil and chemical resistance

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 105 °C
Ambient temperature (assembly)	-20 °C ... 60 °C
Resistance to oil	very good oil and chemical resistance

Approvals

CE

Certificate	CE-compliant
-------------	--------------

Standards and regulations


Resistance to oil	very good oil and chemical resistance
Standard designation	Flame retardancy
Standards/specifications	DIN EN 60332-1-2
	UL 1581
Standard designation	Halogen-free
Standards/specifications	IEC 60754
Standard designation	UV resistance
Standards/specifications	IEC 60068-2-5

Mounting

Assembly note	Outdoors and indoors
---------------	----------------------

Drawings

Dimensional drawing



Drill holes

RAD-PIG-EF316-N-RSMA - Antenna cable



2701402

<https://www.phoenixcontact.com/us/products/2701402>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2701402>



EAC

Approval ID: 19060508

RAD-PIG-EF316-N-RSMA - Antenna cable



2701402

<https://www.phoenixcontact.com/us/products/2701402>

Classifications

ECLASS

ECLASS-13.0	27060310
ECLASS-15.0	27060310

ETIM

ETIM 9.0	EC001682
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

RAD-PIG-EF316-N-RSMA - Antenna cable



2701402

<https://www.phoenixcontact.com/us/products/2701402>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(b)-II, 6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b87a90b6-16c7-43c0-8dea-7ac532134310

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com