

EMD-SL-PH-400 - Monitoring relay



2866077

<https://www.phoenixcontact.com/us/products/2866077>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Monitoring relay for monitoring phase sequence, phase failure and asymmetry, 342...457 V AC, supply from the measurement voltage, 2 changeover contacts

Product description

Increasingly higher demands are being placed on safety and system availability - across all sectors. Processes are becoming more and more complex, not only in mechanical engineering and the chemical industry, but also in plant and automation technology. Demands on power engineering are also increasing constantly.

Error-free and therefore cost-effective operation can only be achieved through continuous monitoring of important network and system parameters. Electronic monitoring relays in the EMD series are available for a wide range of monitoring tasks to avoid the consequences of errors or to keep them within limits.

The operating states are indicated using colored LEDs, errors that may occur can be sent to a control system via a floating contact or can shut down a part of the system. Some device versions are equipped with startup and response delays in order to briefly tolerate measured values outside the set monitoring range.

Your advantages

- Variable supply voltage range

Commercial data

Item number	2866077
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C440
Product key	DK6631
GTIN	4017918952679
Weight per piece (including packing)	149 g
Weight per piece (excluding packing)	149 g
Customs tariff number	85364900
Country of origin	AT

EMD-SL-PH-400 - Monitoring relay



2866077

<https://www.phoenixcontact.com/us/products/2866077>

Technical data

Product properties

Product type	Phase monitoring relay
Operating mode	100% operating factor
Mechanical service life	approx. 2×10^7 cycles

Insulation characteristics

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Electrical properties

Service life electrical	2×10^5 cycles at ohmic load, 1000 VA
Maximum power dissipation for nominal condition	1 W
Mains type	3-phase
Rated insulation voltage	300 V
Rated surge voltage	4 kV

Supply

Supply voltage	From the measured voltage
Nominal power consumption	9 VA

Input data

Input name	Measuring input
Measured value	AC sine (48 Hz ... 63 Hz)
Nominal input voltage U_N	400 V (3 N ~ 400/230 V)
Maximum input voltage	3 N ~ 457/264 V
Input resistance of voltage input	15 k Ω
Frequency range	48 Hz ... 63 Hz
Setting range for response delay	≤ 350 ms (fixed setting)
Setting range for starting delay	≤ 500 ms (fixed setting)
Min setting range of the voltage threshold value	342 V AC
Max. setting range of the voltage threshold value	457 V AC
Function	Phase sequence
	Phase failure
	Asymmetry
Asymmetry	fixed, approx. 30 %
Recovery time	< 100 ms

Output data

Switching

Contact switching type	2 floating changeover contacts
Maximum switching voltage	250 V AC (in acc. with IEC 60664-1)

EMD-SL-PH-400 - Monitoring relay



2866077

<https://www.phoenixcontact.com/us/products/2866077>

Interrupting rating (ohmic load) max.	750 VA (3 A/250 V AC, module aligned, ≤ 5 mm spacing)
	1250 VA (5 A/250 V AC, module not aligned, ≥ 5 mm spacing)
Output fuse	5 A (fast-blow)

Connection data

Connection method	Screw connection
Stripping length	8 mm
Conductor cross-section rigid	0.5 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.25 mm ² ... 2.5 mm ²
Conductor cross-section AWG	20 ... 14

Dimensions

Width	22.5 mm
Height	90 mm
Depth	113 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide PA, self-extinguishing

Environmental and real-life conditions

Ambient conditions

Degree of protection (Housing)	IP40 (Housing)
Degree of protection (Connection terminal blocks)	IP20 (Connection terminal blocks)
Ambient temperature (operation)	-25 °C ... 55 °C
	-25 °C ... 40 °C (corresponds to UL 508)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Climatic class	3K3 (in acc. with EN 60721)
Permissible humidity (operation)	15 % ... 85 %

Approvals

CE

Certificate	CE-compliant
-------------	--------------

UL, USA/Canada

Identification	UL/C-UL Listed UL 508
----------------	-----------------------

EMC data

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive
Noise immunity	EN 61000-6-2

Noise emission

Standards/regulations	EN 61000-6-3
-----------------------	--------------

EMD-SL-PH-400 - Monitoring relay



2866077

<https://www.phoenixcontact.com/us/products/2866077>

Standards and regulations

Standards/regulations	EN 50178
-----------------------	----------

Mounting

Mounting type	DIN rail mounting
Assembly note	on standard DIN rail NS 35 in accordance with EN 60715
Mounting position	any

EMD-SL-PH-400 - Monitoring relay


2866077

<https://www.phoenixcontact.com/us/products/2866077>



Drawings

Block diagram



EMD-SL-PH-400 - Monitoring relay



2866077

<https://www.phoenixcontact.com/us/products/2866077>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2866077>



EAC

Approval ID: RU*C-DE.*08.B.00010



UL Listed

Approval ID: FILE E 172140



cUL Listed

Approval ID: FILE E 172140

EMD-SL-PH-400 - Monitoring relay



2866077

<https://www.phoenixcontact.com/us/products/2866077>

Classifications

ECLASS

ECLASS-13.0	27371803
ECLASS-15.0	27371803

ETIM

ETIM 9.0	EC001441
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

EMD-SL-PH-400 - Monitoring relay



2866077

<https://www.phoenixcontact.com/us/products/2866077>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	3.938 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com