

# PLC-RSC-120UC/21-21AU/MS - Relay module



2910511

<https://www.phoenixcontact.com/us/products/2910511>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLC-INTERFACE, consisting of a relay base and pluggable multilayer gold contact relay with manual operation, integrated status LED, Screw connection, 2 changeover contacts, Bridge rectifier, Input voltage: 120 V AC / 110 V DC

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2910511                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 10 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | C461                           |
| Product key                          | DK623D                         |
| GTIN                                 | 4055626486659                  |
| Weight per piece (including packing) | 79.8 g                         |
| Weight per piece (excluding packing) | 67 g                           |
| Customs tariff number                | 85364900                       |
| Country of origin                    | DE                             |

## Technical data

### Product properties

|                         |                           |
|-------------------------|---------------------------|
| Product type            | Relay Module              |
| Product family          | PLC-INTERFACE             |
| Application             | Palm switch               |
| Operating mode          | 100% operating factor     |
| Mechanical service life | 5x 10 <sup>6</sup> cycles |

### Insulation characteristics: Standards/regulations

|                      |                                       |
|----------------------|---------------------------------------|
| Insulation           | Safe isolation, reinforced insulation |
| Overvoltage category | III                                   |
| Pollution degree     | 2                                     |

### Data management status

|                              |            |
|------------------------------|------------|
| Date of last data management | 12.09.2025 |
|------------------------------|------------|

### Electrical properties

|                                                      |                                                                              |
|------------------------------------------------------|------------------------------------------------------------------------------|
| Maximum power dissipation for nominal condition      | 0.54 W                                                                       |
| Test voltage (Winding/contact)                       | 4 kV <sub>rms</sub> (50 Hz, 1 min., winding/contact)                         |
| Test voltage (Changeover contact/changeover contact) | 2.5 kV <sub>rms</sub> (50 Hz, 1 min., changeover contact/changeover contact) |

### Standards/regulations

|                          |          |
|--------------------------|----------|
| Rated insulation voltage | 250 V AC |
| Rated surge voltage      | 6 kV     |

### Input data

#### Coil side

|                                                      |                                    |
|------------------------------------------------------|------------------------------------|
| Nominal input voltage U <sub>N</sub>                 | 120 V AC                           |
|                                                      | 110 V DC                           |
| Input voltage range                                  | 96 V AC ... 168 V AC (20 °C)       |
|                                                      | 93.5 V DC ... 154 V DC (20 °C)     |
| Nominal voltage (plugged-in electromechanical relay) | 110 V DC                           |
| Drive and function                                   | monostable                         |
| Drive (polarity)                                     | polarized                          |
| Typical input current at U <sub>N</sub>              | 5 mA                               |
| Typical response time                                | 6 ms (110 V DC)                    |
|                                                      | 3 ms ... 15 ms (120 V AC)          |
| Typical release time                                 | 10 ms (110 V DC)                   |
| Typical release time range                           | 3 ms ... 15 ms (120 V AC)          |
| Protective circuit                                   | Bridge rectifier; Bridge rectifier |
| Operating voltage display                            | Yellow LED                         |

### Output data

# PLC-RSC-120UC/21-21AU/MS - Relay module



2910511

<https://www.phoenixcontact.com/us/products/2910511>

## Switching

|                             |                        |
|-----------------------------|------------------------|
| Contact switching type      | 2 changeover contacts  |
| Type of switch contact      | Single contact         |
| Contact material            | AgNi, hard gold-plated |
| Maximum switching voltage   | 30 V AC                |
|                             | 36 V DC                |
| Minimum switching voltage   | 12 V (1 mA)            |
| Limiting continuous current | 50 mA                  |
| Maximum inrush current      | 50 mA                  |
| Min. switching current      | 1 mA (12 V)            |

## Switching: when the gold layer is destroyed

|                                       |                                                                  |
|---------------------------------------|------------------------------------------------------------------|
| Note                                  | the following values are applicable if a gold layer is destroyed |
| Maximum switching voltage             | 250 V AC/DC                                                      |
| Minimum switching voltage             | 12 V (10 mA)                                                     |
| Limiting continuous current           | 6 A                                                              |
| Maximum inrush current                | 12 A (20 ms)                                                     |
| Min. switching current                | 10 mA (12 V)                                                     |
| Interrupting rating (ohmic load) max. | 192 W (24 V DC)                                                  |
|                                       | 62 W (48 V DC)                                                   |
|                                       | 42 W (60 V DC)                                                   |
|                                       | 55 W (110 V DC)                                                  |
|                                       | 66 W (220 V DC)                                                  |
|                                       | 2000 VA (250 V AC)                                               |
| Switching capacity                    | 1 A (24 V (DC13))                                                |
|                                       | 1.5 A (230 V, AC15)                                              |

## Connection data

|                                  |                                                               |
|----------------------------------|---------------------------------------------------------------|
| Connection method                | Screw connection                                              |
| Stripping length                 | 8 mm                                                          |
| Screw thread                     | M3                                                            |
| Conductor cross-section rigid    | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                  |
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                  |
|                                  | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Single ferrule)  |
|                                  | 2x 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (TWIN ferrule) |
| Conductor cross-section AWG      | 26 ... 14                                                     |
| Tightening torque                | 0.6 Nm ... 0.8 Nm                                             |

## Dimensions

|        |        |
|--------|--------|
| Width  | 14 mm  |
| Height | 80 mm  |
| Depth  | 104 mm |

# PLC-RSC-120UC/21-21AU/MS - Relay module



2910511

<https://www.phoenixcontact.com/us/products/2910511>

## Material specifications

|                                                  |                 |
|--------------------------------------------------|-----------------|
| Color                                            | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing)    |

## Environmental and real-life conditions

### Ambient conditions

|                                              |                                |
|----------------------------------------------|--------------------------------|
| Degree of protection (Relay)                 | RT II (Relay)                  |
| Degree of protection (Relay base)            | IP20 (Relay base)              |
| Degree of protection (Installation location) | ≥ IP54 (Installation location) |
| Ambient temperature (operation)              | -20 °C ... 55 °C               |
| Ambient temperature (storage/transport)      | -20 °C ... 85 °C               |
| Altitude                                     | ≤ 2000 m                       |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### UKCA

|             |                |
|-------------|----------------|
| Certificate | UKCA-compliant |
|-------------|----------------|

### UL, USA

|                |                   |
|----------------|-------------------|
| Identification | UL 508            |
|                | UL 508 Recognized |

### UL, USA/Canada

|                |                   |
|----------------|-------------------|
| Identification | UL 508            |
|                | UL 508 Recognized |

### Shipbuilding approval

|             |            |
|-------------|------------|
| Certificate | TAE0000196 |
|-------------|------------|

### Corrosive gas test

|                |                            |
|----------------|----------------------------|
| Identification | ISA-S71.04. G3 Harsh Group |
|                | EN 60068-2-60              |

### Shipbuilding data

|             |                                                                                         |
|-------------|-----------------------------------------------------------------------------------------|
| Temperature | D                                                                                       |
| Humidity    | A                                                                                       |
| Vibration   | B/C                                                                                     |
| EMC         | B                                                                                       |
| Enclosure   | Required protection according to the Rules shall be provided upon installation on board |

## EMC data

|                               |                                        |
|-------------------------------|----------------------------------------|
| Electromagnetic compatibility | Conformance with EMC directive         |
| Low Voltage Directive         | Conformance with Low Voltage Directive |

# PLC-RSC-120UC/21-21AU/MS - Relay module



2910511

<https://www.phoenixcontact.com/us/products/2910511>

## Standards and regulations

### Standards/regulations


|                       |          |
|-----------------------|----------|
| Standards/regulations | EN 50178 |
|-----------------------|----------|

## Mounting

|                   |                           |
|-------------------|---------------------------|
| Mounting type     | DIN rail mounting         |
| Assembly note     | in rows with zero spacing |
| Mounting position | any                       |

## Drawings


Diagram




① DC coils

② AC coils

Operating voltage range




Interrupting rating



Electrical service life




Diagram



Service life reduction factor

Diagram



Permissible humidity for operation and storage.


The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures  $\leq 0^{\circ}\text{C}$  must be prevented

Area B: Condensation at ambient temperatures  $> 0^{\circ}\text{C}$  must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature  $\leq 25^{\circ}\text{C}$ .

Circuit diagram



# PLC-RSC-120UC/21-21AU/MS - Relay module



2910511

<https://www.phoenixcontact.com/us/products/2910511>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2910511>



**EAC**

Approval ID: RU\*C-DE.\*08.B.00010



**DNV GL**

Approval ID: TAE0000196



**cULus Listed**

Approval ID: E140324

# PLC-RSC-120UC/21-21AU/MS - Relay module



2910511

<https://www.phoenixcontact.com/us/products/2910511>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371601 |
| ECLASS-15.0 | 27371601 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001437 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                             |
|-------------------------------------|---------------------------------------------|
| REACH candidate substance (CAS No.) | Hexahydromethylphthalic anhydride(CAS: n/a) |
|                                     | Lead(CAS: 7439-92-1)                        |
| SCIP                                | 0ca4a4cc-802d-4d7c-b1ec-b61143c3265b        |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)