

EV-RCM-6DC-WAT - Differential current monitoring



1309697

<https://www.phoenixcontact.com/us/products/1309697>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX control modular, the residual current monitoring module is used for AC and DC residual current detection in AC charging points. The higher-level safety equipment (e.g., residual current device) is protected against potential DC residual currents.

Commercial data

Item number	1309697
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	EM01
Product key	XWBRYA
GTIN	4063151560669
Weight per piece (including packing)	67.6 g
Weight per piece (excluding packing)	72.4 g
Customs tariff number	85437090
Country of origin	CN

Technical data

Product properties

Product type	Residual current monitoring module
Product family	CHARX control modular
Application	Residual current monitoring module for detecting AC and DC residual voltages in 50/60 Hz AC installations
Manufacturer	Western Automation
Manufacturer Designation	RCM14-03
Number of charging points	1
Charging standard	Type 2
Charging mode	Mode 3

System properties

Charging controllers

Number of charging points	1
---------------------------	---

Electrical properties

Type of charging current	AC
Power consumption	min. 60 mW

Measuring current transducer

Diameter of measuring coil	14 mm
----------------------------	-------

Measuring range: Residual current

Residual current $I_{\Delta n}$	30 mA (AC)
	6 mA (DC)
Rated current I_n	100 A (1-phase)
	40 A (3-phase)

Supply

Supply voltage range	10.8 V DC ... 13.2 V DC (nominal voltage range)
Nominal power consumption	60 mW
Frequency range	50 Hz ... 60 Hz

Connection data

Conductor connection

Connection method	Pin strip 4-pos.
Conductor cross-section AWG	26

Interfaces

Number of interfaces	2 (Error/Test)
----------------------	----------------

Dimensions

Width	60.7 mm
-------	---------

EV-RCM-6DC-WAT - Differential current monitoring



1309697

<https://www.phoenixcontact.com/us/products/1309697>

Height	33.6 mm
Depth	32.50 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

Approvals

Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

Standards and regulations

Standards

Standards/regulations	IEC 62955
-----------------------	-----------

Mounting

Mounting position	any
-------------------	-----

1309697

<https://www.phoenixcontact.com/us/products/1309697>

Classifications

ECLASS

ECLASS-13.0	27144703
ECLASS-15.0	27144703

ETIM

ETIM 9.0	EC002889
----------	----------

UNSPSC

UNSPSC 21.0	39121800
-------------	----------

EV-RCM-6DC-WAT - Differential current monitoring



1309697

<https://www.phoenixcontact.com/us/products/1309697>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com