

AKG 35 YE - Connection terminal block



3063002

<https://www.phoenixcontact.com/us/products/3063002>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connection terminal block, nom. voltage: 300 V, nominal current: 125 A, connection method: Screw connection, Rated cross section: 35 mm², cross section: 2.5 mm² - 35 mm², mounting: Neutral busbar, color: yellow

Commercial data

Item number	3063002
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BE7331
GTIN	4046356558402
Weight per piece (including packing)	20.08 g
Weight per piece (excluding packing)	20.11 g
Country of origin	PL

AKG 35 YE - Connection terminal block



3063002

<https://www.phoenixcontact.com/us/products/3063002>

Technical data

Product properties

Product type	Installation terminal block
Number of connections	1
Number of rows	1

Electrical properties

Maximum load current	125 A (with 35 mm ² conductor cross-section)
Maximum power dissipation for nominal condition	4.06 W
Nominal current I _N	125 A
Current carrying capacity of the neutral busbar	140 A

Connection data

Nominal cross section	35 mm ²
Maximum load current	125 A (with 35 mm ² conductor cross-section)

Level 1 above 1 below 1

Connection method	Screw connection
Screw thread	M6
Tightening torque	3.2 ... 3.7 Nm
Stripping length	16 mm
Connection in acc. with standard	IEC / EN
Conductor cross-section rigid	2.5 mm ² ... 35 mm ²
Cross section AWG	12 ... 2 (converted acc. to IEC)
Conductor cross-section flexible	2.5 mm ² ... 35 mm ²
Conductor cross-section, flexible [AWG]	12 ... 2 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	2.5 mm ² ... 35 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	2.5 mm ² ... 35 mm ²
2 conductors with same cross section, solid	1.5 mm ² ... 16 mm ²
2 conductors with same cross section, flexible	1.5 mm ² ... 16 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	1.5 mm ² ... 16 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm ² ... 10 mm ²
Nominal current	125 A
Maximum load current	125 A (with 35 mm ² conductor cross-section)
Nominal voltage	300 V
Nominal cross section	35 mm ²

Dimensions


AKG 35 YE - Connection terminal block



3063002

<https://www.phoenixcontact.com/us/products/3063002>

Dimensional drawing



Width	14.3 mm
Height	27 mm
Depth	39 mm
Length	27 mm

Material specifications

Color	yellow (RAL 1018)
Flammability rating according to UL 94	V2
Insulating material	PA

Standards and regulations


Connection in acc. with standard	IEC / EN
----------------------------------	----------

Mounting

Mounting type	Neutral busbar
---------------	----------------

Drawings


Dimensional drawing



AKG 35 YE - Connection terminal block

3063002

<https://www.phoenixcontact.com/us/products/3063002>



AKG 35 YE - Connection terminal block



3063002

<https://www.phoenixcontact.com/us/products/3063002>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3063002>

 CSA Approval ID: 13631				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	-	135 A	18 - 2	-

 UL Recognized Approval ID: E60425				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
B				
	-	115 A	18 - 2	-
C				
	-	115 A	18 - 2	-
F				
	-	115 A	18 - 2	-

 EAC Approval ID: KZ7500651131219505				
---	--	--	--	--

AKG 35 YE - Connection terminal block



3063002

<https://www.phoenixcontact.com/us/products/3063002>

Classifications

ECLASS

ECLASS-13.0	27250116
ECLASS-15.0	27250116

ETIM

ETIM 9.0	EC000001
----------	----------

UNSPSC

UNSPSC 21.0	31162900
-------------	----------

AKG 35 YE - Connection terminal block



3063002

<https://www.phoenixcontact.com/us/products/3063002>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com