

# SACC-M12MR-4CON-PG7-M - Connector



1681101

<https://www.phoenixcontact.com/us/products/1681101>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Connector, Universal, 4-position, Plug angled M12, coding: A, Screw connection, knurl material: Zinc die-cast, nickel-plated, cable gland Pg7, external cable diameter 4 mm ... 6 mm



## Your advantages

- Safe use in the field, thanks to a high degree of protection
- Screw connection: proven connection technology for a large selection of different conductors

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1681101       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF30          |
| Product key                          | AF2CAA        |
| GTIN                                 | 4017918157487 |
| Weight per piece (including packing) | 23.76 g       |
| Weight per piece (excluding packing) | 23.01 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# SACC-M12MR-4CON-PG7-M - Connector



1681101

<https://www.phoenixcontact.com/us/products/1681101>

## Technical data

### Notes

Assembly note

**NOTE:** Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

### Mounting

Assembly note

The connector pin assignment can be rotated 90° to the cable outlet

### Product properties


|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Sensor type          | Universal                       |
| Number of positions  | 4                               |
| No. of cable outlets | 1                               |
| Shielded             | no                              |
| Coding               | A                               |
| Cable outlet         | angled                          |
| Pg screw connection  | Pg7                             |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Dimensions

Dimensional drawing



Length

41 mm

### External dimensions

Outside diameter

4 mm ... 6 mm

### Housing

Diameter housing

20 mm

### Material specifications

|                                        |      |
|----------------------------------------|------|
| Flammability rating according to UL 94 | HB   |
| Seal material                          | NBR  |
| Material of grip body                  | PA   |
| Contact material                       | CuZn |

# SACC-M12MR-4CON-PG7-M - Connector



1681101

<https://www.phoenixcontact.com/us/products/1681101>

|                               |                              |
|-------------------------------|------------------------------|
| Contact surface material      | CuSnZn                       |
| Contact carrier material      | PA                           |
| Material for screw connection | Zinc die-cast, nickel-plated |

## Connection data

### Conductor connection

|                                         |                                                                 |
|-----------------------------------------|-----------------------------------------------------------------|
| Connection method                       | Screw connection                                                |
| Connection cross section                | 0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> (without ferrule) |
|                                         | 0.14 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> (with ferrule)    |
|                                         | 0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> (solid)           |
| Connection cross section AWG            | 24 ... 18 (without ferrule)                                     |
|                                         | 26 ... 20 (with ferrule)                                        |
| Stripping length of the individual wire | 5 mm                                                            |
| Tightening torque                       | 0.4 Nm (M12 knurl)                                              |
|                                         | 0.2 Nm (Screw terminal blocks)                                  |
|                                         | 0.8 Nm ... 1 Nm (Pressure screw with sleeve housing)            |

## Electrical properties

|                                |          |
|--------------------------------|----------|
| Rated surge voltage            | 2.5 kV   |
| Contact resistance             | ≤ 8 mΩ   |
| Insulation resistance          | ≥ 100 MΩ |
| Nominal voltage U <sub>N</sub> | 250 V AC |
|                                | 250 V DC |
| Nominal current I <sub>N</sub> | 4 A      |

## Mechanical properties

### Mechanical data

|                             |      |
|-----------------------------|------|
| Insertion/withdrawal cycles | ≥ 50 |
|-----------------------------|------|

## Connector

### Connection 1

|                   |        |
|-------------------|--------|
| Head design       | Plug   |
| Head cable outlet | angled |
| Head thread type  | M12    |
| Coding            | A      |

## Cable/line

|                                         |           |
|-----------------------------------------|-----------|
| Signal type/category                    | Universal |
| Stripping length of the individual wire | 5 mm      |

## Environmental and real-life conditions

### Ambient conditions

|                      |      |
|----------------------|------|
| Degree of protection | IP67 |
|----------------------|------|

# SACC-M12MR-4CON-PG7-M - Connector



1681101

<https://www.phoenixcontact.com/us/products/1681101>

|                                                                   |                                  |
|-------------------------------------------------------------------|----------------------------------|
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 85 °C (Plug / socket) |
|-------------------------------------------------------------------|----------------------------------|

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |


# SACC-M12MR-4CON-PG7-M - Connector

1681101

<https://www.phoenixcontact.com/us/products/1681101>

## Drawings

Dimensional drawing




M12 x 1 male plug, angled

# SACC-M12MR-4CON-PG7-M - Connector


1681101

<https://www.phoenixcontact.com/us/products/1681101>



Male/Female M12

Schematic diagram




Cable connection side M12 (screw connection)

# SACC-M12MR-4CON-PG7-M - Connector

1681101

<https://www.phoenixcontact.com/us/products/1681101>

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

# SACC-M12MR-4CON-PG7-M - Connector



1681101

<https://www.phoenixcontact.com/us/products/1681101>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1681101>

|       |                                                                                                                                       |                       |                   |                             |
|-------|---------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-------------------|-----------------------------|
| keine |  <b>cUL Recognized</b><br>Approval ID: FILE E 221474 |                       |                   |                             |
|       | Nominal voltage $U_N$                                                                                                                 | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|       | 250 V                                                                                                                                 | 4 A                   | -                 | -                           |

|       |                                                                                                                                      |                       |                   |                             |
|-------|--------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-------------------|-----------------------------|
| keine |  <b>UL Recognized</b><br>Approval ID: FILE E 221474 |                       |                   |                             |
|       | Nominal voltage $U_N$                                                                                                                | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|       | 250 V                                                                                                                                | 4 A                   | -                 | -                           |

# SACC-M12MR-4CON-PG7-M - Connector



1681101

<https://www.phoenixcontact.com/us/products/1681101>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-M12MR-4CON-PG7-M - Connector



1681101

<https://www.phoenixcontact.com/us/products/1681101>

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 1e14d1be-0ad5-4cfd-8d34-ac3e4e626fac |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)