

0824632

<https://www.phoenixcontact.com/us/products/0824632>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Your advantages

- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications
- The UC-TMF ... UniCard labeling range includes markers for products with tall and flat marker grooves

Commercial data

Item number	0824632
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8117
GTIN	4046356359672
Weight per piece (including packing)	8.045 g
Weight per piece (excluding packing)	8.7 g
Country of origin	PL

UC-TMF 4 GN CUS - Marker for terminal blocks



0824632

<https://www.phoenixcontact.com/us/products/0824632>

Technical data

Product properties

Product type	Klemmenmarker
Pitch	4.2 mm

Marking

Number of individual labels	120
Number of individual labels per row	15
Identification technology	UV LED technology

Dimensions

Width	3.60 mm
Height	6.50 mm
Depth	1.60 mm
Pitch	4.2 mm

Material specifications

Color	green (RAL 6021)
Material	PA
Flammability rating according to UL 94	V2
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

UC-TMF 4 GN CUS - Marker for terminal blocks



0824632

<https://www.phoenixcontact.com/us/products/0824632>

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is

UC-TMF 4 GN CUS - Marker for terminal blocks



0824632

<https://www.phoenixcontact.com/us/products/0824632>

	recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

Mounting

Mounting type	snap into flat marker groove
---------------	------------------------------

UC-TMF 4 GN CUS - Marker for terminal blocks

0824632

<https://www.phoenixcontact.com/us/products/0824632>

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

UC-TMF 4 GN CUS - Marker for terminal blocks



0824632

<https://www.phoenixcontact.com/us/products/0824632>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UC-TMF 4 GN CUS - Marker for terminal blocks



0824632
<https://www.phoenixcontact.com/us/products/0824632>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.061 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com