


UC1-TMF 5 BU CUS - Marker for terminal blocks



0828341

<https://www.phoenixcontact.com/us/products/0828341>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, can be ordered: by sheet, blue, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 5.2 mm, Number of individual labels: 96, text field height: 5.2 mm, text field width: 4.45 mm

Your advantages

- The UC1-TMF ... UniCard labeling range includes markers for Weidmüller, Wago, ABB (entrelec), Conta-Clip, and Klemmsan terminal blocks
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications
- The markers support multi-line labeling
- The sheets provide space for including function texts

Commercial data

Item number	0828341
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8117
GTIN	4046356485241
Weight per piece (including packing)	6.79 g
Weight per piece (excluding packing)	6.29 g
Country of origin	PL

UC1-TMF 5 BU CUS - Marker for terminal blocks



0828341

<https://www.phoenixcontact.com/us/products/0828341>

Technical data

Product properties

Product type	Klemmenmarker
Pitch	5.2 mm

Marking

Number of individual labels	96
Number of individual labels per row	12
Identification technology	UV LED technology

Dimensions

Width	4.45 mm
Height	5.20 mm
Depth	2.20 mm
Pitch	5.2 mm

Material specifications

Color	blue (RAL 5015)
Material	PA
Flammability rating according to UL 94	V2
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

UC1-TMF 5 BU CUS - Marker for terminal blocks



0828341

<https://www.phoenixcontact.com/us/products/0828341>

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

UC1-TMF 5 BU CUS - Marker for terminal blocks



0828341

<https://www.phoenixcontact.com/us/products/0828341>

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Standards	
Standards/regulations	EN 45545-2

Mounting

Mounting type	snap into flat marker groove
---------------	------------------------------

UC1-TMF 5 BU CUS - Marker for terminal blocks

0828341

<https://www.phoenixcontact.com/us/products/0828341>

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

UC1-TMF 5 BU CUS - Marker for terminal blocks



0828341

<https://www.phoenixcontact.com/us/products/0828341>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UC1-TMF 5 BU CUS - Marker for terminal blocks



0828341
<https://www.phoenixcontact.com/us/products/0828341>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.065 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com