

UCT-TM 3,5 BU - Marker for terminal blocks



0829508

<https://www.phoenixcontact.com/us/products/0829508>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, Sheet, blue, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: latching, for terminal block width: 3.5 mm, Number of individual labels: 102, text field height: 10.5 mm, text field width: 2.95 mm

Your advantages

- The UCT-TM... UniCard labeling range includes markers for Phoenix Contact products with tall marker grooves, e.g. terminals
- The markers, which are supplied in uniform sheets, can be marked quickly, easily, and precisely using the card printers
- The sheets provide additional space for project information and function text that can be helpful during further assembly
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

Item number	0829508
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG07
Product key	BG2118
GTIN	4046356595032
Weight per piece (including packing)	14.96 g
Weight per piece (excluding packing)	13.79 g
Customs tariff number	39269097
Country of origin	PL

UCT-TM 3,5 BU - Marker for terminal blocks



0829508

<https://www.phoenixcontact.com/us/products/0829508>

Technical data

Notes

General	Can be labeled via thermal transfer
---------	-------------------------------------

Product properties

Product type	Klemmenmarker
Pitch	3.5 mm

Marking

Number of individual labels	102
Number of individual labels per row	17
Identification technology	Thermotransfer

Dimensions

Width	2.95 mm
Height	10.50 mm
Depth	4.60 mm
Pitch	3.5 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V0
Base element material	PC
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

UCT-TM 3,5 BU - Marker for terminal blocks



0829508

<https://www.phoenixcontact.com/us/products/0829508>

Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Standards

UCT-TM 3,5 BU - Marker for terminal blocks



0829508

<https://www.phoenixcontact.com/us/products/0829508>

Standards/regulations	EN 45545-2
-----------------------	------------

Mounting

Mounting type	latching
---------------	----------

UCT-TM 3,5 BU - Marker for terminal blocks



0829508

<https://www.phoenixcontact.com/us/products/0829508>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UCT-TM 3,5 BU - Marker for terminal blocks



0829508
<https://www.phoenixcontact.com/us/products/0829508>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.003 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com