

US-EMP (100X15) YE - Snap-in markers



0829522

<https://www.phoenixcontact.com/us/products/0829522>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Snap-in markers, Card, yellow, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: latching, Number of individual labels: 9, text field height: 15 mm, text field width: 100 mm

Your advantages

- The US-EMP ... UniSheet labeling range includes markers that can be fitted into existing CARRIER EMP ... label frames
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The perforated markers and labels are easy to separate and can be easily fitted
- The sheets provide space for including function texts

Commercial data

Item number	0829522
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2419
GTIN	4046356613651
Weight per piece (including packing)	15.78 g
Weight per piece (excluding packing)	15.63 g
Customs tariff number	39204910
Country of origin	DE

US-EMP (100X15) YE - Snap-in markers



0829522

<https://www.phoenixcontact.com/us/products/0829522>

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Marking

Number of individual labels	9
Number of individual labels per row	1
Identification technology	Thermotransfer

Dimensions

Width	104.00 mm
Height	14.90 mm
Depth	0.50 mm

Material specifications

RoHS compliant	yes
Foil strength	500 µm
Color	yellow (RAL 1018)
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05 (following)
Result	Test passed
Climate level	AHT 1.0 S

US-EMP (100X15) YE - Snap-in markers



0829522

<https://www.phoenixcontact.com/us/products/0829522>

Cycles	2
--------	---

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10 ... 25 °C / 35 ... 65 % relative humidity. Storage in a cool and dry place is recommended.
Recommended ambient temperature (storage/transport)	10 °C ... 25 °C
Recommended humidity (storage/transport)	35 % ... 65 %
Shelf life	12 months (see packaging date)

Mounting

Mounting type	latching
---------------	----------

US-EMP (100X15) YE - Snap-in markers



0829522

<https://www.phoenixcontact.com/us/products/0829522>

Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

US-EMP (100X15) YE - Snap-in markers



0829522
<https://www.phoenixcontact.com/us/products/0829522>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.027 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com