

# EMLC (40X8)R YE CUS - Fabric label



0830163

<https://www.phoenixcontact.com/us/products/0830163>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



## Your advantages

- The EMLC label consists of a textile foil with very low restoring forces
- Enables labels to be stuck over edges and curves
- Labeling service: Phoenix Contact can custom-label all EMLC ... markers in accordance with your requirements

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0830163                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | BG8141                         |
| GTIN                                 | 4046356627542                  |
| Weight per piece (including packing) | 1.99 g                         |
| Weight per piece (excluding packing) | 1.99 g                         |
| Country of origin                    | PL                             |

## Technical data

### Product properties

|                  |                     |
|------------------|---------------------|
| Product type     | Gerätemarker        |
| Product property | Low restoring force |

### Marking

|                                     |   |
|-------------------------------------|---|
| Number of individual labels per row | 2 |
|-------------------------------------|---|

### Dimensions

|        |          |
|--------|----------|
| Width  | 40.00 mm |
| Height | 8.00 mm  |
| Depth  | 0.15 mm  |
| Length | 8 mm     |

### Material specifications

|            |                                |
|------------|--------------------------------|
| Color      | yellow (RAL 1018)              |
| Material   | PA                             |
| Components | free from silicone and halogen |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### Test for substances that would hinder coating with paint or varnish

|               |                                       |
|---------------|---------------------------------------|
| Result        | Test passed                           |
| Specification | DIN EN ISO 1518-1:2019-10 (following) |
| Requirements  | ≥ 5 N                                 |
| Result        | Test passed                           |

#### UV resistance

|                         |                                    |
|-------------------------|------------------------------------|
| Specification           | ISO 4892-2:2013-03 (following)     |
| Result                  | Test passed                        |
| Test duration           | 96 h                               |
| Procedure               | Artificial irradiation.            |
| Specification           | IEC 60068-2-78:2012-10 (following) |
| Result                  | Test passed                        |
| Duration                | 96 h                               |
| Temperature for testing | 40 °C                              |
| Relative humidity       | 93 %                               |

#### Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 125 °C (150 °C) | Test passed                     |

# EMLC (40X8)R YE CUS - Fabric label



0830163

<https://www.phoenixcontact.com/us/products/0830163>

## Wipe resistance of inscriptions

|                                                   |                                                |
|---------------------------------------------------|------------------------------------------------|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|                                                   | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed                                    |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed                                    |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                    |
| Specification                                     | ISO 175:2010 (following)                       |
| Test duration                                     | 168 h                                          |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed                                    |
| IRM 901                                           | Test passed                                    |
| IRM 902                                           | Test passed                                    |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |
| Test duration | 96 h                      |

## Ambient conditions

|                                                     |                                                                                 |
|-----------------------------------------------------|---------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | 0 °C ... 125 °C                                                                 |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                           |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life                                          | 2 years                                                                         |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# EMLC (40X8)R YE CUS - Fabric label



0830163

<https://www.phoenixcontact.com/us/products/0830163>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# EMLC (40X8)R YE CUS - Fabric label



0830163  
<https://www.phoenixcontact.com/us/products/0830163>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)