

PML-W204 (100X100) - Warning label

0830446

<https://www.phoenixcontact.com/us/products/0830446>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Warning label, Sheet, yellow/black, labeled: Lightning flash and print: 120 V, mounting type: adhesive, diameter: 0 mm, Number of individual labels: 9



Commercial data

Item number	0830446
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG21
Product key	BG2511
GTIN	4046356717700
Weight per piece (including packing)	22.13 g
Weight per piece (excluding packing)	22.13 g
Customs tariff number	39199080
Country of origin	DE

PML-W204 (100X100) - Warning label

0830446

<https://www.phoenixcontact.com/us/products/0830446>



Technical data

Product properties

Product type	Plant marker
Area of application	Warning labels
Type	Warning identification according to ISO 7010

Marking

Number of individual labels	9
Number of individual labels per row	2
Printing	Lightning flash and print: 120 V
Identification technology	Office laser printing

Dimensions

Width	100 mm
Height	118.5 mm

Material specifications

RoHS compliant	yes
Foil strength	50 µm
Adhesive	Acrylic
Color	yellow/black
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

PML-W204 (100X100) - Warning label

0830446

<https://www.phoenixcontact.com/us/products/0830446>



Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Shelf life	2 years

Mounting

Mounting type	adhesive
---------------	----------

PML-W204 (100X100) - Warning label

0830446

<https://www.phoenixcontact.com/us/products/0830446>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com