

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, Strip, white, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: latching, Number of individual labels: 20, text field height: 12 mm, text field width: 6 mm

Your advantages

- The markers, which are supplied in uniform strips, can be printed onto quickly and easily using the BLUEMARK printing systems
- The UM6M-TM ... UM labeling range includes terminal markers for ABB terminal blocks
- The multi-section marking strips are easy to fit and can be easily separated if required
- The markers support multi-line labeling

Commercial data

Item number	0830926
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG08
Product key	BGE21C
GTIN	4046356910613
Weight per piece (including packing)	2.22 g
Weight per piece (excluding packing)	2.22 g
Customs tariff number	39269097
Country of origin	PL

UM6M-TM (6X12) - Marker for terminal blocks



0830926

<https://www.phoenixcontact.com/us/products/0830926>

Technical data

Product properties

Product type	Klemmenmarker
Area of application	ABB

Marking

Number of individual labels	20
Number of individual labels per row	10
Number of marker strips	2
Identification technology	UV LED technology

Dimensions

Width	5.57 mm
Height	11.90 mm
Depth	2.50 mm

Material specifications

RoHS compliant	yes
Color	white (RAL 9010)
Flammability rating according to UL 94	V2
Base element material	PC
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed

UM6M-TM (6X12) - Marker for terminal blocks



0830926

<https://www.phoenixcontact.com/us/products/0830926>

Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	latching
---------------	----------

UM6M-TM (6X12) - Marker for terminal blocks



0830926

<https://www.phoenixcontact.com/us/products/0830926>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UM6M-TM (6X12) - Marker for terminal blocks



0830926
<https://www.phoenixcontact.com/us/products/0830926>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.009 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com