

# US-PML-W100 (100X100) CUS - Warning label

1014130

<https://www.phoenixcontact.com/us/products/1014130>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Warning label, can be ordered: by card, yellow/black, labeled according to customer specifications: Blank, mounting type: adhesive, Number of individual labels: 1, text field height: 100 mm, text field width: 100 mm



## Your advantages

- UniSheet - stick-on warning labels, marked according to customer specifications
- Suitable for indoor and outdoor use
- The warning labels conform to the ISO 7010 international standard
- Highly flexible, soft PVC label that adapts well to uneven surfaces

## Commercial data

Item number	1014130
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8159
GTIN	4046356786713
Weight per piece (including packing)	5.98 g
Weight per piece (excluding packing)	5.11 g
Country of origin	PL

# US-PML-W100 (100X100) CUS - Warning label

1014130

<https://www.phoenixcontact.com/us/products/1014130>



## Technical data

### Product properties

Product type	Plant marker
Area of application	Warning labels
Type	Warning identification according to ISO 7010

### Marking

Number of individual labels	1
Printing	Blank
Identification technology	Thermotransfer

### Dimensions

Width	92.31 mm
Height	81.35 mm
Depth	0.08 mm

### Material specifications

Foil strength	60 µm
Adhesive strength	25 µm
Adhesive	Acrylic
Color	yellow/black
Base element material	PVC
Components	Silicone-free

### Environmental and real-life conditions

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

### Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

### Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

# US-PML-W100 (100X100) CUS - Warning label

1014130

<https://www.phoenixcontact.com/us/products/1014130>



## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

## Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (assembly)	> 10 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

## Mounting

Mounting type	adhesive
---------------	----------

# US-PML-W100 (100X100) CUS - Warning label

1014130

<https://www.phoenixcontact.com/us/products/1014130>



## Classifications

### ECLASS

ECLASS-15.0	40200203
ECLASS-13.0	40200203

### ETIM

ETIM 9.0	EC001777
----------	----------

### UNSPSC

UNSPSC 21.0	55121700
-------------	----------

# US-PML-W100 (100X100) CUS - Warning label

1014130

<https://www.phoenixcontact.com/us/products/1014130>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)