

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/us/products/1079591>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 6, Pin, Push-in connection, 100 V, 20 A, 1.5 mm² ... 4 mm², with short-circuit function

Commercial data

Item number	1079591
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	AF7ACE
GTIN	4055626800387
Weight per piece (including packing)	33.4 g
Weight per piece (excluding packing)	30 g
Customs tariff number	85366990
Country of origin	CN

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/us/products/1079591>

Technical data

Notes

General	Please observe the circuit diagram
General	Use at least 1.5 mm ² cables with a maximum conductor loop of 2 m. No open conductor loops permitted!
General	only use flexible conductors with ferrules

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

Product properties

Product type	Modular contact insert
Series	HC-M-TSC
Number of positions	6
Connection profile	6
Number of module slots	2
Contact material type	rolled

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data


Connection technology

Connection technology	Push-in connection
-----------------------	--------------------

Conductor connection

Conductor cross section	1.5 mm ² ... 4 mm ²
Connection cross section AWG	21 ... 12
Stripping length of the individual wire	8 mm

Dimensions

Dimensional drawing	
Width	33.8 mm
Height	45.8 mm
Length	29.2 mm

Mechanical characteristics

Contact diameter	4 mm
------------------	------

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/us/products/1079591>

Electrical properties

Rated voltage (III/3)	100 V (when plugged in)
	100 V (Unplugged and during plugging)
Rated surge voltage	1.5 kV
Rated current	20 A (When plugged in)
	20 A (Unplugged and during plugging)

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)
---------------------------------	--


HC-TSC-M-06-PT-M - Contact insert module

1079591

<https://www.phoenixcontact.com/us/products/1079591>


Drawings

Dimensional drawing




Male insert

Diagram




Derating diagram (mated)

Diagram



Derating diagram (unmated)

Circuit diagram



Circuit diagram

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/us/products/1079591>

Classifications

ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

ETIM

ETIM 9.0	EC000438
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

HC-TSC-M-06-PT-M - Contact insert module



1079591
<https://www.phoenixcontact.com/us/products/1079591>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com