

AXL SE DOR2 W 230 - Relay module



1105562

<https://www.phoenixcontact.com/us/products/1105562>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline Smart Elements, Relay module, Relay outputs: 2 (floating), Changeover contact, 220 V DC, 230 V AC, degree of protection: IP20

Product description

You can integrate Axioline Smart Elements into systems with the Smart Element interface. This Smart Element has two relay changeover contacts that are independent of each other and floating. You can install low-voltage and extra-low-voltage modules directly next to each other on one Axioline F backplane.

Your advantages

- 2 mono-stable relays
- Floating connections for 2 actuators
- Switching current per channel: 6 A, maximum
- Device rating plate stored

Commercial data

Item number	1105562
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR05
Product key	DRIB34
GTIN	4055626989013
Weight per piece (including packing)	44 g
Weight per piece (excluding packing)	42.95 g
Customs tariff number	85364900
Country of origin	DE

AXL SE DOR2 W 230 - Relay module


1105562

<https://www.phoenixcontact.com/us/products/1105562>



Technical data

Dimensions

Dimensional drawing		
Width		14.9 mm
Height		62.2 mm
Depth		62 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Interfaces

Smart Element interface

Number of interfaces	1
Connection method	Card edge connector
Transmission speed	See system in which you use the Smart Element.
Start time until ready to operate	< 500 ms

System properties

Module

ID code (hex)	none
Process data channel	8 bit
Input address area	0 Byte
Output address area	1 Byte
Required parameter data	9 Byte
Required configuration data	6 Byte

Output data

Relay

Number of outputs	2 (floating)
Connection method	Push-in connection
Connection technology	2-conductor
Contact switching type	Changeover contact
Switching current	max. 6 A (up to 250 V AC, cos phi = 0.75 ... 0.8)
	max. 6 A (up to 30 V DC, N/O contact, general use)

AXL SE DOR2 W 230 - Relay module



1105562

<https://www.phoenixcontact.com/us/products/1105562>

	max. 3 A (up to 30 V DC, N/C contact, general use)
	max. 580 mA (at 48 V DC)
	max. 250 mA (at 110 V DC)
	max. 125 mA (at 220 V DC)
	max. 220 mA DC (125 V DC, L/R ≤ 50 ms)
	max. 110 mA DC (250 V DC, L/R ≤ 50 ms)
Switching power	max. 1500 VA (AC applications up to 55°C, observe derating above that)
	max. 180 W (up to 30 V DC, N/O contact, general use)
	max. 90 W (up to 30 V DC, N/C contact, general use)
	max. 28 W (above 30 V DC)
	For further DC values, see DC load limit curve.
Switching capacity in accordance with IEC 60947-5-1	3 A (24 V (AC15))
	3 A (120 V (AC15))
	3 A (230 V (AC15))
	2 A (24 V (DC13), L/R = 100 ms)
	0.2 A (110 V (DC13), L/R = 44 ms)
	0.1 A (220 V (DC13), L/R = 44 ms)
Switching capacity in accordance with UL/CSA 61010-2-201	5 A (AC, B300, up to max. 55°C)
	1 A (DC, R300, up to max. 60°C)
Switching frequency	max. 6 (per minute)
Mechanical service life	20x 10 ⁶ cycles

Product properties

Product type	I/O component
Product family	Axioline Smart Elements
Type	modular
Mounting position	See the system in which the Smart Element is used.

Insulation characteristics

Overvoltage category	III (EN 61010-2-201/IEC 61010-2-201)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

Electrical properties

Maximum power dissipation for nominal condition	2 W
---	-----

Potentials: Communications power supply of the Smart Elements (U_{SE})

Supply voltage	using card edge connectors
----------------	----------------------------

Potentials: I/O supply (U_P)

Supply voltage	24 V DC (using card edge connectors)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	typ. 36 mA (18 mA per relay, all contacts floating)
Protective circuit	Surge protection; See the system in which the Smart Element is used.
	Reverse polarity protection; parallel diode

AXL SE DOR2 W 230 - Relay module



1105562

<https://www.phoenixcontact.com/us/products/1105562>

Electrical isolation/isolation of the voltage ranges

Test voltage: Communications supply / 24 V supply (I/O)	500 V AC, 50 Hz, 1 min
Test voltage: Communications supply / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply (I/O) / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: Supply logic / relay contact	4 kV
Test voltage: 24 V supply (devices) / relay contact	4 kV
Test voltage: Relay contact / functional ground	4 kV

Connection data

Connection technology

Connection name	I/O
Note on the connection method	Please observe the information provided on conductor cross-sections in the "Axioline Smart Elements" user manual. When selecting the cables, observe the permissible operating temperature in accordance with IEC or UL.

Conductor connection

Connection method	Push-in connection
Conductor cross-section rigid	0.25 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.25 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16
Conductor cross-section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1.5 mm ²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 0.75 mm ²
Stripping length	8 mm

I/O

Connection method	Push-in connection
Note on the connection method	Please observe the information provided on conductor cross-sections in the "Axioline Smart Elements" user manual. When selecting the cables, observe the permissible operating temperature in accordance with IEC or UL.
Conductor cross-section, rigid	0.25 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.25 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 0.75 mm ²
Conductor cross-section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1.5 mm ²
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 106 kPa

AXL SE DOR2 W 230 - Relay module



1105562

<https://www.phoenixcontact.com/us/products/1105562>

Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

Mounting

Mounting type	Plug-in mounting (Smart Element slot)
Mounting position	See the system in which the Smart Element is used.

AXL SE DOR2 W 230 - Relay module


1105562

<https://www.phoenixcontact.com/us/products/1105562>



Drawings

Dimensional drawing



Dimensions (in mm)

AXL SE DOR2 W 230 - Relay module



1105562

<https://www.phoenixcontact.com/us/products/1105562>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1105562>



cULus Listed

Approval ID: E238705

AXL SE DOR2 W 230 - Relay module



1105562

<https://www.phoenixcontact.com/us/products/1105562>

Classifications

ECLASS

ECLASS-13.0	27242604
ECLASS-15.0	27242604

ETIM

ETIM 9.0	EC001599
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

AXL SE DOR2 W 230 - Relay module



1105562

<https://www.phoenixcontact.com/us/products/1105562>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	803dadcf-6223-4d53-89fd-02c84ab2202c

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com