


AI 0,5-8 OG-S - Ferrule



1212784

<https://www.phoenixcontact.com/us/products/1212784>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Taped ferrules, 0.5 mm², sleeve length: 8 mm, with plastic collars, according to DIN 46228-4, special color: orange, with function end for safe and convenient processing with the Crimphandy, 20 strips each with 50 sleeves per strip.

Your advantages

- The corresponding taped ferrules for the Crimphandy are suitable for use on all modular terminal blocks, particularly those from the CLIPLINE complete system
- The ferrules with plastic sleeve are made from soft tin-plated electrolytic copper

Commercial data

Item number	1212784
Packing unit	1,000 pc
Minimum order quantity	1,000 pc
Product key	BH3415
GTIN	4046356958691
Weight per piece (including packing)	0.1 g
Weight per piece (excluding packing)	0.097 g
Country of origin	DE

AI 0,5-8 OG-S - Ferrule



1212784


<https://www.phoenixcontact.com/us/products/1212784>

Technical data

Product properties

Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	Specifically for processing with our CF CRIMPHANDY
	UL certified
	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of DIN 46228-1 and UL 486F in terms of size
	Plastic collar made of polypropylene
	Halogen-free
Long/short-term temperature: +105°C/+120°C	

Dimensions

Dimensional drawing	
Sleeve length	14 mm
Length contact range	8 mm
Ferrule diameter	1.1 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.25 mm
Inner dimensions of the insulating collar	2.5 mm

Material specifications

Color	orange (RAL 2003)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

Mechanical properties

Technical data

Sleeve length	14 mm
---------------	-------

Environmental and real-life conditions

Ambient conditions

Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)
Short-term temperature	120 °C

AI 0,5-8 OG-S - Ferrule



1212784

<https://www.phoenixcontact.com/us/products/1212784>

Standards and regulations

Design according to standard	UL 486F-E, Sonderfarbe
------------------------------	------------------------

AI 0,5-8 OG-S - Ferrule


1212784

<https://www.phoenixcontact.com/us/products/1212784>



Drawings

Dimensional drawing



AI 0,5-8 OG-S - Ferrule



1212784

<https://www.phoenixcontact.com/us/products/1212784>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212784>



cULus Listed

Approval ID: E488001

AI 0,5-8 OG-S - Ferrule



1212784

<https://www.phoenixcontact.com/us/products/1212784>

Classifications

ECLASS

ECLASS-13.0	27400201
ECLASS-15.0	27400201

ETIM

ETIM 9.0	EC000005
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

AI 0,5-8 OG-S - Ferrule



1212784
<https://www.phoenixcontact.com/us/products/1212784>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com