

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet



1379294

<https://www.phoenixcontact.com/us/products/1379294>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect universal, AC type 1, Vehicle charging inlet, 80 A , 250 V AC, Single wires, length: 5 m, locking actuator: 12 V, 4-pos., Front and rear mounting, M6, housing: black, for charging electric vehicles with alternating current (AC), IEC 62196-2, SAE J1772, A protective cap is supplied as standard for the AC contacts.

## Product description

Vehicle charging inlet for charging with alternating current (AC), compatible with type 1 AC vehicle charging connectors (EVSE), for installation in electric vehicles (EV).

## Your advantages

- Complete product range
- Uniform, space-saving dimensions for the installation space and the screw connection points of all Phoenix Contact vehicle charging inlets
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Integrated interlock during charging
- Manual emergency release of the locking actuator
- Protected and sealed against dirt and water with a high degree of protection

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1379294       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | EM01          |
| Product key                          | XWCAIA        |
| GTIN                                 | 4063151747770 |
| Weight per piece (including packing) | 22.22 g       |
| Weight per piece (excluding packing) | 2,379 g       |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet



1379294

<https://www.phoenixcontact.com/us/products/1379294>

## Technical data

### Notes

|         |                                                               |
|---------|---------------------------------------------------------------|
| General | A protective cap is supplied as standard for the AC contacts. |
|---------|---------------------------------------------------------------|

### Product properties

|                     |                                                                                                            |
|---------------------|------------------------------------------------------------------------------------------------------------|
| Product type        | Vehicle charging inlet                                                                                     |
| Product family      | CHARX connect universal                                                                                    |
| Application         | for charging electric vehicles with alternating current (AC)<br>for installation in electric vehicles (EV) |
| Charging standard   | AC type 1                                                                                                  |
| Charging mode       | Mode 2, 3                                                                                                  |
| Customer variations | On request                                                                                                 |

### Electrical properties

|                               |                                          |
|-------------------------------|------------------------------------------|
| Note on the connection method | Crimp connection, cannot be disconnected |
| Temperature monitoring        | AC contacts: PTC chain (DIN EN 60738-1)  |

### Charging power and current (AC charging (1-phase))

|                          |                   |
|--------------------------|-------------------|
| Type of charging current | AC single-phase   |
| Charging current         | 80 A AC (1-phase) |
| Charging power           | 20 kW             |

### Pin assignment (Leistungskontakte)

|               |               |
|---------------|---------------|
| Number        | 3 (L1, N, PE) |
| Rated voltage | 250 V AC      |
| Rated current | 80 A AC       |

### Pin assignment (Signalkontakte)

|                             |                                                                                                                 |
|-----------------------------|-----------------------------------------------------------------------------------------------------------------|
| Type of signal transmission | Pulse width modulation with modulated Powerline communication in accordance with ISO/IEC 15118 / DIN SPEC 70121 |
| Number                      | 2 (CP, CS)                                                                                                      |
| Rated voltage               | 30 V AC                                                                                                         |
| Rated current               | 2 A                                                                                                             |
| Coding                      | 2.7 k $\Omega$ (between PE and CS)                                                                              |
| Insulation resistance       | > 200 M $\Omega$                                                                                                |

### Locking actuator

|                                          |                                     |
|------------------------------------------|-------------------------------------|
| Locking actuator                         | 12 V, 4-pos.<br>Top center position |
| Possible power supply range at the motor | 9 V ... 16 V                        |
| Maximum voltage for locking detection    | 12 V                                |
| Typical motor current for locking        | 0.25 A                              |
| Reverse current of the motor             | max. 1.5 A                          |
| Max. dwell time with reverse current     | 1 s                                 |

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet



1379294

<https://www.phoenixcontact.com/us/products/1379294>

|                                     |                     |
|-------------------------------------|---------------------|
| Recommended adaptation time         | 600 ms              |
| Pause time after entry or exit path | 3 s                 |
| Service life insertion cycles       | > 10000 load cycles |
| Lock recognition                    | available           |
| Mechanical emergency release        | available           |
| Ambient temperature (operation)     | -40 °C ... 80 °C    |

## Temperature sensors (PTC chain)

|                              |                                           |
|------------------------------|-------------------------------------------|
| Sensor type                  | PTC chain                                 |
| Standards/regulations        | DIN EN 60738-1                            |
| Attachment point             | Sensor for the AC contacts                |
| Measuring range_resistance   | 790 $\Omega$ ... 1420 $\Omega$            |
| Resistance                   | max. 1200 $\Omega$ $\pm$ 5 K              |
| Recommended measured current | $\leq$ 1 mA ( $U_{\text{max}}$ = 16 V DC) |
| Ambient temperature          | -40 °C ... 130 °C (Operation)             |

## Dimensions

### Vehicle charging inlet

|        |          |
|--------|----------|
| Width  | 90 mm    |
| Height | 90 mm    |
| Depth  | 112.2 mm |

### Bore dimensions

|        |       |
|--------|-------|
| Width  | 73 mm |
| Height | 73 mm |
| Depth  | 73 mm |

## Material specifications

|                            |              |
|----------------------------|--------------|
| Color (Housing)            | black (9005) |
| Color (Mating face)        | black (9005) |
| Material (Housing)         | Plastic      |
| Material (Contact surface) | Silver       |

## Cable/line

|              |              |
|--------------|--------------|
| Cable length | 5 m          |
| Cable type   | Single wires |

### Single-core wires for AC

|                         |                          |
|-------------------------|--------------------------|
| Cable length            | 5 m                      |
| Cable structure         | 2 x 16 mm <sup>2</sup>   |
| Single wire, material   | Silicone                 |
| Single wire, color      | OG                       |
| External cable diameter | 9.90 mm $\pm$ 0.3 mm     |
| Cable resistance        | $\leq$ 1.16 $\Omega$ /km |

### Single-core wire for PE

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet



1379294

<https://www.phoenixcontact.com/us/products/1379294>

|                         |                        |
|-------------------------|------------------------|
| Cable length            | 5 m                    |
| Cable structure         | 1 x 16 mm <sup>2</sup> |
| Single wire, material   | Silicone               |
| Single wire, color      | GN/YE                  |
| External cable diameter | 7.00 mm ±0.2 mm        |
| Cable resistance        | ≤ 1.16 Ω/km            |

## Single-core wires for locking actuator

|                         |                            |
|-------------------------|----------------------------|
| Cable length            | 1.5 m                      |
| Cable structure         | 4 x 0.5 mm <sup>2</sup>    |
| Single wire, material   | PVC                        |
| Single wire, color      | BU/RD, BU/GN, BU/YE, BU/BN |
| External cable diameter | 1.60 mm ±0.20 mm           |
| Cable resistance        | ≤ 37.1 Ω/m                 |

## Single-core wires for temperature sensors

|                         |                         |
|-------------------------|-------------------------|
| Cable length            | 1 m                     |
| Cable structure         | 5 x 0,5 mm <sup>2</sup> |
| Single wire, color      | BN/GY                   |
|                         | BN/YE/GN                |
| External cable diameter | 1.60 mm ±0.20 mm        |
| Cable resistance        | ≤ 37.1 Ω/m              |

## Single-core wires for communication

|                         |                         |
|-------------------------|-------------------------|
| Cable length            | 1 m                     |
| Cable structure         | 2 x 0.5 mm <sup>2</sup> |
| Single wire, material   | PVC                     |
| Single wire, color      | BK                      |
|                         | WH                      |
| External cable diameter | 1.60 mm ±0.20 mm        |
| Cable resistance        | ≤ 37.1 Ω/m              |

## Mechanical properties

### Mechanical data

|                             |         |
|-----------------------------|---------|
| Insertion/withdrawal cycles | > 10000 |
| Insertion force             | < 75 N  |
| Withdrawal force            | < 75 N  |

## Environmental and real-life conditions

### Ambient conditions

|                                               |                                                                                                                                                                                                                |
|-----------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Degree of protection (Vehicle charging inlet) | IP55 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products) |
|                                               | IP67 (Inner area of vehicle charging inlet)                                                                                                                                                                    |

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet



1379294

<https://www.phoenixcontact.com/us/products/1379294>

|                                         |                          |
|-----------------------------------------|--------------------------|
| Ambient temperature (operation)         | -40 °C ... 60 °C         |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C         |
| Altitude                                | 4000 m (above sea level) |

## Standards and regulations

### Standards

|                       |             |
|-----------------------|-------------|
| Standards/regulations | IEC 62196-2 |
|                       | SAE J1772   |

## Mounting

|                                          |                                                                       |
|------------------------------------------|-----------------------------------------------------------------------|
| Mounting type                            | Front and rear mounting (0 to 90 degree frontal inclination possible) |
| Mounting hole diameter                   | 6.70 mm (ø)                                                           |
| Fixing screws                            | M6                                                                    |
| Screws included in the scope of delivery | none                                                                  |

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet




1379294

<https://www.phoenixcontact.com/us/products/1379294>


## Drawings

Dimensional drawing



Dimensional drawing

Connection diagram




Pin assignment of vehicle charging inlets

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet

1379294


<https://www.phoenixcontact.com/us/products/1379294>

Connection diagram



Installation positions

Connection diagram




Terminology definition

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet

1379294

<https://www.phoenixcontact.com/us/products/1379294>

Functional drawing




Operating instructions

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet

1379294

<https://www.phoenixcontact.com/us/products/1379294>

Schematic diagram




Detection for Vehicle Connector

CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet




1379294  
<https://www.phoenixcontact.com/us/products/1379294>

Schematic diagram



Block diagram of the locking actuator

Schematic diagram




Temperature sensor technology resistance range at AC contacts

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet

1379294

<https://www.phoenixcontact.com/us/products/1379294>



Locking states of the locking actuator

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet



1379294  
<https://www.phoenixcontact.com/us/products/1379294>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27144706 |
| ECLASS-15.0 | 27144706 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002898 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121800 |
|-------------|----------|

# CHARX T1HCI12-1AC80-5,0M1 - Vehicle charging inlet



1379294

<https://www.phoenixcontact.com/us/products/1379294>

## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 6(c), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                                             |
|-------------------------------------|-------------------------------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                                        |
|                                     | Bis(2-(2-methoxyethoxy)ethyl)ether(CAS: 143-24-8)           |
|                                     | 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) |
| SCIP                                | 58ca9b1d-ee5f-4426-9dc5-503c1bbd7a5f                        |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)