

SAC-3P-M12MS/0,6-PUR/A-1L-Z110 - Sensor/actuator cable



1400738

<https://www.phoenixcontact.com/us/products/1400738>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: A, with 1 LED, on Valve connector A, with 1 LED, Wiring: Z diode, cable length: 0.6 m

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1400738 |
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| Product key | AF1DJA |
| GTIN | 4046356510264 |
| Weight per piece (including packing) | 51.4 g |
| Weight per piece (excluding packing) | 51.4 g |
| Country of origin | PL |

SAC-3P-M12MS/0,6-PUR/A-1L-Z110 - Sensor/actuator cable



1400738

<https://www.phoenixcontact.com/us/products/1400738>

Technical data

Product properties

| | |
|----------------------|--|
| Product type | Sensor/actuator cable with valve connector |
| Number of positions | 3 |
| No. of cable outlets | 1 |
| Shielded | no |
| Coding | A |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Connection data

Conductor connection

| | |
|-------------------|--------------------------|
| Tightening torque | 0.4 Nm (M12 connector) |
| | 0.6 Nm (Valve connector) |

Material specifications

| | |
|--|------------------------------|
| Flammability rating according to UL 94 | HB |
| Seal material | TPU |
| Material housing valve plug | TPU |
| Material of grip body | TPU |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Contact carrier material | TPU GF |
| Contact material | CuSn |
| Valve plug contact insert material | PA 6.6 |
| Contact surface material | Sn |
| Material for screw connection | Zinc die-cast, nickel-plated |

Electrical properties

| | |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 48 V AC |
| Nominal current I_N | 4 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|----------------------------|
| Insertion/withdrawal cycles | ≥ 100 (M12 connector) |
|-----------------------------|----------------------------|

Signaling

| | |
|----------------|-------|
| Status display | 1 LED |
|----------------|-------|

SAC-3P-M12MS/0,6-PUR/A-1L-Z110 - Sensor/actuator cable



1400738

<https://www.phoenixcontact.com/us/products/1400738>

| | |
|------------------------|-----|
| Status display present | yes |
|------------------------|-----|

Connector

Connection 1

| | |
|---------------------|-------------------|
| Type | Plug straight M12 |
| Number of positions | 3 |
| Coding type | A |

Connection 2

| | |
|---------------------|---|
| Type | Valve connector A |
| Number of positions | 3 |
| Material | CuSn (Contact) Sn (Contact surface) PA 6.6 (Contact carrier) TPU (Housing) |
| Protective circuit | Z diode |

Cable/line

| | |
|--------------|-------|
| Cable length | 0.6 m |
|--------------|-------|

PUR halogen-free black [PUR]

| | |
|---------------------------------|--|
| Dimensional drawing |  |
| Cable weight | 30 kg/km |
| UL AWM Style | 20549 |
| Number of positions | 3 |
| Shielded | no |
| Cable type | PUR halogen-free black [PUR] |
| Conductor structure signal line | 28x 0.15 mm |
| AWG signal line | 20 |
| Conductor cross section | 3x 0.5 mm ² |
| Wire diameter incl. insulation | 1.5 mm ±0.05 mm (Signal line) |
| External cable diameter | 4.50 mm ±0.2 mm |
| Outer sheath, material | PUR |
| External sheath, color | black-gray RAL 7021 |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | PP |
| Single wire, color | black 1, black 2, green/yellow |

SAC-3P-M12MS/0,6-PUR/A-1L-Z110 - Sensor/actuator cable



1400738

<https://www.phoenixcontact.com/us/products/1400738>

| | |
|---|---|
| Overall twist | 3 wires, twisted |
| Max. conductor resistance | 39 Ω/km (at 20 °C) |
| Insulation resistance | min. 20 MΩ*km |
| Nominal voltage, cable | ≤ 300 V |
| Test voltage | ≥ 1200 V |
| Minimum bending radius, fixed installation | 5 x D |
| Minimum bending radius, flexible installation | 10 x D |
| Smallest bending radius, fixed installation | 22.5 mm |
| Smallest bending radius, movable installation | 45 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 15000000, Bending radius: 50 mm, Traversing path: 0.9 m, Traversing rate: 5 m/s, Acceleration: 30 m/s ² |
| Halogen-free | in accordance with DIN VDE 0472 part 815 |
| Flame resistance | according to DIN VDE 0482 |
| | According to DIN EN 50265-2-1 |
| Resistance to oil | in accordance with DIN EN 60811-2-1 |
| Other resistance | largely oil-resistant |
| | partly UV-resistant (in accordance with DIN EN ISO 4892-2-A) |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation) -20 °C ... 80 °C (Cable, flexible installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------------------------|
| Degree of protection | IP65 |
| | IP67 |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket) |
| Ambient temperature (operation) (Valve connector) | -20 °C ... 85 °C (Valve connector) |

Standards and regulations

| | |
|--------------------------|-----------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |
| Standard designation | Valve connector |
| Standards/specifications | EN 175301-803 |

SAC-3P-M12MS/0,6-PUR/A-1L-Z110 - Sensor/actuator cable




1400738

<https://www.phoenixcontact.com/us/products/1400738>


Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



Valve connector, type A


SAC-3P-M12MS/0,6-PUR/A-1L-Z110 - Sensor/actuator cable



1400738


<https://www.phoenixcontact.com/us/products/1400738>

Dimensional drawing



Valve connector, type A, side view

Schematic diagram




Pin assignment M12 plug, 3-pos., valve connector

1400738


<https://www.phoenixcontact.com/us/products/1400738>

Schematic diagram



Valve connector pin assignment, type A

Circuit diagram



Contact assignment of M12 plug and valve connector

SAC-3P-M12MS/0,6-PUR/A-1L-Z110 - Sensor/actuator cable



1400738

<https://www.phoenixcontact.com/us/products/1400738>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060312 |
| ECLASS-15.0 | 27060312 |

ETIM

| | |
|----------|----------|
| ETIM 8.0 | EC001855 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31251500 |
|-------------|----------|

SAC-3P-M12MS/0,6-PUR/A-1L-Z110 - Sensor/actuator cable



1400738

<https://www.phoenixcontact.com/us/products/1400738>

Environmental product compliance

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com