

FL IF 2FX SC-F - Media module



2832412

<https://www.phoenixcontact.com/us/products/2832412>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fiber optic interface module for connecting 100 Base-FX multi-mode glass fibers (1300 nm), SC, connection direction forward

Your advantages

- Robust Ethernet transmission even for medium-range environments prone to interference

Commercial data

Item number	2832412
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN17
Product key	DNN123
GTIN	4017918974466
Weight per piece (including packing)	102.9 g
Weight per piece (excluding packing)	80 g
Customs tariff number	85176200
Country of origin	DE

FL IF 2FX SC-F - Media module



2832412

<https://www.phoenixcontact.com/us/products/2832412>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Extension module
Type	Stand-alone
Basic functions	Media module for modular managed switch

System properties

Functionality

Basic functions	Media module for modular managed switch
-----------------	---

Electrical properties

Electrical isolation	100Base-FX // supply
Local diagnostics	LEDs at head station / extension module
Maximum power dissipation for nominal condition	21.6 W
Test voltage	2 kV AC
Transmission medium	Copper
	FO

Supply

Supply voltage	via head station
Power supply connection	from FL SWITCH GHS or FXT
Typical current consumption	200 mA

Interfaces

Ethernet: 100Base-FX in acc. with IEEE 802.3

Transmission length	10000 m (maximum (depends on the fiber used))
---------------------	---

Ethernet: 100Base-FX in acc. with IEEE 802.3

Connection method	SC
Transmission speed	100 Mbps
Transmission length	2800 m (fiberglass with F-G 50/125 1.6 dB/km F800)
	6400 m (fiberglass with F-G 50/125 0.7 dB/km F1200)
	3000 m (fiberglass with F-G 62.5/125 2.6 dB/km F600)
	2800 m (fiberglass with F-G 50/125 1.6 dB/km F800)
Wavelength	1300 nm
No. of channels	2 (SC multi-mode)

Dimensions


FL IF 2FX SC-F - Media module



2832412

<https://www.phoenixcontact.com/us/products/2832412>

Dimensional drawing



Width	31 mm
Height	75.7 mm
Depth	72.5 mm

Material specifications

Color	green
Flammability rating according to UL 94	V0
Housing material	PA

Mechanical tests

Shock in accordance with EN 60068-2-27/IEC 60068-2-27	: Operation: 25g, 11 ms duration, semi-sinusoidal shock impulse
	: Storage/Transport: 50g, 11 ms duration, semi-sinusoidal shock impulse

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C (non-condensing)
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion B
	IEC 61000-4-3 (immunity to radiated interference) Criterion A
	IEC 61000-4-4 (burst) Criterion A
	IEC 61000-4-5 (surge) Criterion A
	IEC 61000-4-6 (immunity to conducted interference) Criterion A
	IEC 61000-4-8 (immunity to magnetic fields) Criterion A
	EN 55022 (emitted interference) Criterion A
Noise immunity	EN 61000-6-2:2005

Noise emission

Standards/regulations	EN 61000-6-3/-4
-----------------------	-----------------

FL IF 2FX SC-F - Media module



2832412

<https://www.phoenixcontact.com/us/products/2832412>

Standards and regulations


Free from substances that could impair the application of coating	In acc. with VW specification
Electrical isolation	100Base-FX // supply

Mounting

Mounting type	In the host system
---------------	--------------------

Drawings

Dimensional drawing



The figure shows a version of the interface module with the head station FL SWITCH MM HS

FL IF 2FX SC-F - Media module



2832412

<https://www.phoenixcontact.com/us/products/2832412>

Classifications

ECLASS

ECLASS-13.0	19170411
-------------	----------

ETIM

ETIM 9.0	EC001467
----------	----------

UNSPSC

UNSPSC 21.0	43201500
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------