


UMK-32 RM/MR-G24/1/YCS - Active module



2969055

<https://www.phoenixcontact.com/us/products/2969055>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



32-channel output relay module (one N/O contact, 250 V AC/3 A) with a screw connection. The module is controlled through a 50-pos. system connector and is suitable for the Yokogawa ADV 551 and ADV 561 cards.

Commercial data

Item number	2969055
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK219N
GTIN	4046356163699
Weight per piece (including packing)	549.2 g
Weight per piece (excluding packing)	411.8 g
Customs tariff number	85364190
Country of origin	DE

UMK-32 RM/MR-G24/1/YCS - Active module



2969055

<https://www.phoenixcontact.com/us/products/2969055>

Technical data

Product properties

Product type	Interface module
No. of channels	32
Compatible components	Miniature relay, REL-MR-G 24/1
With components	yes

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Rated insulation voltage	300 V AC
Rated surge voltage	4 kV (Basic insulation)

Supported controller YOKOGAWA CS3000 CentumVP

Suitable I/O card	ADV551
	ADV561

Supported controller YOKOGAWA STARDOM

Suitable I/O card	NFDV551
	NFDV561

Input data

Nominal input voltage U_N	24 V DC
Input voltage range in reference to U_N	0.9 ... 1.1
Input voltage range	21.6 V DC ... 26.4 V DC
Typical input current at U_N	6.5 mA (per channel)
Protective circuit	Free running; Freewheeling diode
	Reverse polarity protection; Polarity protection diode
Operating voltage display	Green LED
Status display/channel	Yellow LED

Output data

Compatible components	Miniature relay, REL-MR-G 24/1
-----------------------	--------------------------------

Switching

Contact switching type	1 N/O contact
Maximum switching voltage	250 V AC
	125 V DC
Minimum switching voltage	5 V AC/DC
Limiting continuous current	3 A
Maximum inrush current	2 A (Supply, (P1+, P2+), pluggable fuse (IEC 127-2, 5X20, 2A))
Min. switching current	1 mA

UMK-32 RM/MR-G24/1/YCS - Active module



2969055

<https://www.phoenixcontact.com/us/products/2969055>

Interrupting rating (ohmic load) max.	72 W (at 24 V DC)
	60 W (at 48 V DC)
	50 W (at 60 V DC)
	50 W (at 110 V DC)
	750 VA (for 250 V AC)
Error detection (line break / short-circuit)	no

Connection data

Field level

Connection method	Screw connection
Number of connections	72
Number of positions	3
Conductor cross-section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	26 ... 14


Controller level

Connection method	Yokogawa, KS compatible
Number of connections	1
Number of positions	50
Note	Usable system cables: Phoenix Contact YUC50, Yokogawa AKB331
Tightening torque	0.5 Nm

Signaling

Status display present	yes
------------------------	-----

Dimensions

Dimensional drawing	
Width	202.5 mm
Height	77 mm
Depth	61 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC, side panel PA non-reinforced,

Environmental and real-life conditions

UMK-32 RM/MR-G24/1/YCS - Active module



2969055

<https://www.phoenixcontact.com/us/products/2969055>

Ambient conditions

Degree of protection	IP00
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	EN 61010-2-201
	IEC 60664

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

Notes

Notes on operation	Observe the maximum switching capacity of the relays used
Notes on operation	Do not connect adjacent channels to SELV/ PELV and voltages dangerous to the touch.
Notes on operation	The outputs are not suitable for switching different line conductors. The sum of the switching voltages used for adjacent outputs must not exceed the rated insulation voltage value
Notes on operation	The necessary requirements for insulation (basic insulation or reinforced insulation) from adjacent modules (in DIN-rail direction) must be realized by applying suitable measures (e. g., partition plates).
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

UMK-32 RM/MR-G24/1/YCS - Active module


2969055

<https://www.phoenixcontact.com/us/products/2969055>




Drawings

Dimensional drawing




Diagram



Derating curve for limiting continuous current

Circuit diagram



UMK-32 RM/MR-G24/1/YCS - Active module



2969055

<https://www.phoenixcontact.com/us/products/2969055>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2969055>



EAC

Approval ID: RU*DE*08.B.01841/19

UMK-32 RM/MR-G24/1/YCS - Active module



2969055

<https://www.phoenixcontact.com/us/products/2969055>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
SCIP	7d1ee103-678c-459c-8062-e7577fbbd41a