

1436356

https://www.phoenixcontact.com/us/products/1436356

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, Universal, 5-position, Socket, straight, M12-Standard, Acoding, on free cable end, Individual wires, cable length: 0.5 m, 0.34 mm^2 , TPE litz wire

Your advantages

- · Preassembled with litz wires for immediate use
- · Customer-specific assemblies and litz wire lengths available
- Standard pin assignments and codings for signal transmission with a uniform design-in design
- For high transmission safety: shield connection to the housing with optional EMC nut

Commercial data

Item number	1436356
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB24
Product key	ABQCPE
GTIN	4046356438322
Weight per piece (including packing)	25.3 g
Weight per piece (excluding packing)	15.4 g
Customs tariff number	85444290
Country of origin	DE



1436356

https://www.phoenixcontact.com/us/products/1436356

Technical data

Notes

otes	
Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
General	Contact connection method: Crimp connection
Safety note	
Safety note	WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.
	 WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
	 WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
	 The products are suitable for applications in plant, controller, and electrical device engineering.
	 When operating the connectors in outdoor applications, they must be separately protected against environmental influences.
	 Assembled products may not be manipulated or improperly opened.
	 Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).
	 When using the product in direct connection with third-party manufacturers, the user is responsible.
	 For operating voltages > 50 V AC, conductive connector housings must be grounded
	 Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.
	Observe the corresponding technical data. You will find information: o On the product o On the packing label o In the supplied documentation o Online at phoenixcontact.com/products under the product
	Only use tools recommended by Phoenix Contact
	Use a protective cap to protect connectors that are not in use.

The suitable accessories are available online in the accessory



1436356

https://www.phoenixcontact.com/us/products/1436356

	section of the product at phoenixcontact.com/products
	 Ensure that the protective or functional ground has been properly connected.
	 VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector
	 The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
Mounting	
Mounting type	Rear mounting (Pg9, with flat nut)
Tightening torque	1.25 Nm 1.5 Nm (Installation-side)
Product proportion	
Product properties Product type	Circular connectors (device side)
Application	Signal
Sensor type	Universal
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	M12
Insulation characteristics	
Overvoltage category	II II
Degree of pollution	3
laterial specifications	
Material Housing	PA 6.6
Material Insulating body	PA 6.6
Material Contact	CuZn
Material Contact surface	Au
Material Seal	Viton
Flammability rating according to UL 94	НВ
Conductor material	Tin-plated Cu litz wires
lectrical properties	
Rated surge voltage	1.5 kV
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	60 V (AC)
	60 V (DC)
Nominal current I _N	4 A



1436356

https://www.phoenixcontact.com/us/products/1436356

Max. conductor resistance	80 Ω/km
Connection data	
Conductor connection	
Connection method	Individual wires
Contact connection type	Socket
Conductor cross-section	0.34 mm²
Tightening torque	1.25 Nm 1.5 Nm (Installation-side)
Mechanical properties	
Mechanical data	
Insertion/withdrawal cycles	> 100
Connector	
Connection 1	
Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	Standard
Coding	A
Connection 2	
Head design	free cable end
Cable/line	
Cable length	0.5 m
Cable type	TPE litz wire
Signal type/category	Universal
Wire diameter incl. insulation	1.2 mm ±0.07 mm
Single wire, color	black, brown,blue, white, gray
Cable cross section	0.34 mm²
Conductor material	Tin-plated Cu litz wires
Conductor structure signal line	7x 0.25 mm
AWG signal line	24
Material wire insulation	TPE
Thickness, insulation	0.21 mm
Nominal voltage, cable	300 V
Test voltage, cable	2000 V AC
Cable resistance	≤ 80 Ω/km
Cable insulation resistance	≥ 20 MΩ*km
Ambient temperature (operation)	-40 °C 85 °C (cable, fixed installation)
	-25 °C 85 °C (Cable, flexible installation)



1436356

https://www.phoenixcontact.com/us/products/1436356

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female	-25 °C 85 °C (Plug / socket)
connector)	-40 °C 85 °C (without mechanical actuation)
Ambient temperature (operation) (Cable, flexible installation)	-25 °C 85 °C (Cable, flexible installation)
Ambient temperature (operation) (Cable, fixed installation)	-40 °C 85 °C (cable, fixed installation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations


Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101




1436356

https://www.phoenixcontact.com/us/products/1436356

Drawings



Pin assignment M12 socket, 5-pos., A-coded, socket side view



I = current strength, T = ambient temperature



1436356

https://www.phoenixcontact.com/us/products/1436356

Circuit diagram



Contact assignment of the M12 socket



1436356

https://www.phoenixcontact.com/us/products/1436356

Classifications

ECLASS

	ECLASS-13.0	27440103
	ECLASS-15.0	27440103
ETIM		
	ETIM 9.0	EC003570
	LTIIVI 9.0	LC003370
UNSPSC		
	UNSPSC 21.0	39121400



1436356

https://www.phoenixcontact.com/us/products/1436356

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a6f446d8-c574-44cd-852f-3ef0fa73ac00

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com