

CC-AT60-S16-R14-NI - Crimp contact



1519754

<https://www.phoenixcontact.com/us/products/1519754>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: AT04, Pin, turned, contact diameter: 1.6 mm, rated current: 13 A, contact material: Cu alloy

Commercial data

Item number	1519754
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF72
Product key	AF2IEB
GTIN	4063151982980
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	0.5 g
Country of origin	MX

CC-AT60-S16-R14-NI - Crimp contact



1519754

<https://www.phoenixcontact.com/us/products/1519754>

Technical data

Notes

General	AT60-215-16141
Assembly note	Crimp with 8-indent crimp tool qualified to MIL-DTL-22520/1, e.g., Daniels AF8-TH1A or Rennsteig 8758 0000 6 (tool) /8758 1102 0 (Multi pin locator)

Product properties

Product type	Crimp contact
Series	AT04 AHD10-9
Contact material type	turned

Connection data


Connection technology

Contact connection type	Pin
-------------------------	-----

Material specifications

Material Contact	Cu alloy
Material Contact surface	Ni

Dimensions

Dimensional drawing	
Diameter (Contact diameter)	1.6 mm

Electrical properties

Rated current	13 A (MAX)
---------------	------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
---------------------------------	-------------------

CC-AT60-S16-R14-NI - Crimp contact


1519754

<https://www.phoenixcontact.com/us/products/1519754>



Drawings

Dimensional drawing



Dimensional drawing

CC-AT60-S16-R14-NI - Crimp contact



1519754

<https://www.phoenixcontact.com/us/products/1519754>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

CC-AT60-S16-R14-NI - Crimp contact



1519754
<https://www.phoenixcontact.com/us/products/1519754>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com