

UC-TMF 12 VT - Marker for terminal blocks



0822686
<https://www.phoenixcontact.com/us/products/0822686>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, Sheet, violet, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snap in, for terminal block width: 12 mm, Number of individual labels: 40

Your advantages

- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications
- The UC-TMF ... UniCard labeling range includes markers for products with tall and flat marker grooves

Commercial data

Item number	0822686
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BG2117
GTIN	4046356328890
Weight per piece (including packing)	8.27 g
Weight per piece (excluding packing)	6 g
Country of origin	PL

UC-TMF 12 VT - Marker for terminal blocks



0822686

<https://www.phoenixcontact.com/us/products/0822686>

Technical data

Product properties

Product type	Klemmenmarker
Pitch	12 mm

Marking

Number of individual labels	40
Number of individual labels per row	5
Identification technology	UV LED technology

Dimensions

Width	11.45 mm
Height	6.50 mm
Depth	1.60 mm
Pitch	12 mm

Material specifications

RoHS compliant	yes
Color	violet (RAL 4005)
Material	PA
Flammability rating according to UL 94	V2
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed

UC-TMF 12 VT - Marker for terminal blocks



0822686

<https://www.phoenixcontact.com/us/products/0822686>

Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	snap in
---------------	---------

UC-TMF 12 VT - Marker for terminal blocks



0822686

<https://www.phoenixcontact.com/us/products/0822686>

Classifications

ETIM

ETIM 8.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UC-TMF 12 VT - Marker for terminal blocks



0822686
<https://www.phoenixcontact.com/us/products/0822686>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com