

MCS-H-40-3031 - Film hinge

1524154

<https://www.phoenixcontact.com/us/products/1524154>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Film hinge, color: orient red (similar RAL 3031), dimensions: 9.2 x 4.2 x 40 mm



Your advantages

- Convenient operation during device installation and maintenance thanks to optional hinges on the housing cover
- Flexible mounting thanks to the optional adapter plate
- Safe operation with the right degree of protection
- Individualized product selection due to the modular system
- Optimized PCB installation: PCB can be installed in a nearly horizontal orientation thanks to the angled housing edge

Commercial data

Item number	1524154
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AC04
Product key	ACFFAZ
GTIN	4063151990633
Weight per piece (including packing)	1.12 g
Weight per piece (excluding packing)	1.12 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Notes

Assembly note	Please observe the assembly instructions available in the download area.
Assembly note	The hinges must be inserted completely into the housing and frame as far as they will go, so that the two-stage opening of the housing functions optimally.
Recommendation	Further information and detailed dimensions are available in the download area.

Product properties

Product type	Mounting material
Housing type	Field housing
Housing series	MCS

Dimensions

Width	9.2 mm
Height	4.2 mm
Depth	40 mm

Material specifications

Color	orient red (RAL 3031)
Material	PP
Flammability rating according to UL 94	HB

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 Hz ... 58.1 Hz)
Acceleration	2g (58.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

Glow-wire test

Specification	IEC 60695-2-11:2021-10
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h

MCS-H-40-3031 - Film hinge



1524154

<https://www.phoenixcontact.com/us/products/1524154>

Force	20 N
-------	------

Mechanical strength / tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	10

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Half-sine
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

Test for substances that would hinder coating with paint or varnish

Specification	VDMA 24364:2018-05
Result	Test passed

Mounting

Mounting type	Plug-in mounting
---------------	------------------

Packaging specifications

Type of packaging	PE bag
-------------------	--------

MCS-H-40-3031 - Film hinge

1524154

<https://www.phoenixcontact.com/us/products/1524154>



Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

MCS-H-40-3031 - Film hinge



1524154
<https://www.phoenixcontact.com/us/products/1524154>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com