

SACB-8/ 8-M23 SH - Distributor box



1526389

<https://www.phoenixcontact.com/us/products/1526389>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, number of slots: 8, number of positions: 4, status display: no

Commercial data

Item number	1526389
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF43
Product key	AF3CDB
GTIN	4017918963835
Weight per piece (including packing)	434.1 g
Weight per piece (excluding packing)	342 g
Customs tariff number	85366990
Country of origin	PL

SACB-8/ 8-M23 SH - Distributor box



1526389

<https://www.phoenixcontact.com/us/products/1526389>

Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
Note on application	Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories".

Product properties

Product type	Distributor box
Number of positions	4
Number of slots	8

Electrical properties

Nominal voltage U_N	48 V
	60 V DC
Rated current, total	12 A
Max. current carrying capacity per path	2 A
Current carrying capacity per slot	4 A

Connection data

Conductor connection	
Tightening torque slot sensor/actuator cable	0.4 Nm

Signaling

Status display present	no
------------------------	----

Material specifications

Flammability rating according to UL 94	V0
--	----

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP65
	IP67

SACB-8/ 8-M23 SH - Distributor box



1526389

<https://www.phoenixcontact.com/us/products/1526389>

Classifications

ECLASS

ECLASS-13.0	27440111
ECLASS-15.0	27440111

UNSPSC

UNSPSC 21.0	31251501
-------------	----------

SACB-8/ 8-M23 SH - Distributor box



1526389

<https://www.phoenixcontact.com/us/products/1526389>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable
Exemption	6(a), 6(a)-I, 6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com