

HC-M-01-PT-F-16 - Contact insert module



1544117

<https://www.phoenixcontact.com/us/products/1544117>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 1, power contacts: 1, control contacts: 0, Socket, Push-in connection, 830 V, 76 A, 2.5 mm² ... 16 mm², application: Power

Commercial data

Item number	1544117
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	AF7ACE
GTIN	4067923017603
Weight per piece (including packing)	31.3 g
Weight per piece (excluding packing)	31.3 g
Customs tariff number	85366990
Country of origin	PL

HC-M-01-PT-F-16 - Contact insert module



1544117

<https://www.phoenixcontact.com/us/products/1544117>

Technical data

Notes

General	For HEAVYCON HC-B6 to B48 housings with a tall design and snap-in retaining frames.
General	Connectors may be operated only when there is no load/voltage.
General	25 mm ² litz wire without ferrule

Product properties

Product type	Modular contact insert
Series	HC-M-01
Application	Power
Number of positions	1
Connection profile	1
Number of module slots	1
No. of power contacts	1
No. of control contacts	0
Contact material type	turned

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data

Connection technology

Connection technology	Push-in connection
-----------------------	--------------------

Conductor connection

Conductor cross section	2.5 mm ² ... 16 mm ² (The cross section specification refers to the geometric cross section of the cable used)
Connection cross section AWG	14 ... 6 (The cross section specification refers to the geometric cross section of the cable used)
Stripping length of the individual wire	19 mm ±1 mm

Dimensions

Width	34 mm
Height	58 mm
Length	15 mm

Mechanical characteristics

Minimum housing height	72 mm
Contact diameter	8 mm

Electrical properties

Rated voltage (III/2) contacts	1000 V
--------------------------------	--------

HC-M-01-PT-F-16 - Contact insert module



1544117

<https://www.phoenixcontact.com/us/products/1544117>

Rated voltage (III/3)	830 V
Rated surge voltage	8 kV
Rated current	76 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC
Standards/regulations	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------


Standards and regulations

Testing

Standards/regulations	PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)
-----------------------	---


Drawings

Diagram



Derating diagram for flexible conductors

Diagram



Derating diagram for flexible conductors with ferrule

HC-M-01-PT-F-16 - Contact insert module



1544117

<https://www.phoenixcontact.com/us/products/1544117>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1544117>

 CSA Approval ID: 158887				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	1000 V	76 A	- 6	-

HC-M-01-PT-F-16 - Contact insert module



1544117

<https://www.phoenixcontact.com/us/products/1544117>

Classifications

ECLASS

ECLASS-13.0	27440217
ECLASS-15.0	27440217

ETIM

ETIM 9.0	EC000438
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-M-01-PT-F-16 - Contact insert module



1544117
<https://www.phoenixcontact.com/us/products/1544117>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com