

HC-CME-DD-107-F-SNAP-L - Conductor connector



1549644

<https://www.phoenixcontact.com/in/products/1549644>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor connector, number of positions: 107+PE, number of connections per position: 1, Socket, Crimp connection, 250 V, 10 A, 0.14 mm² ... 2.5 mm², for connections in control cabinets

Commercial data

Item number	1549644
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	AF7ABZ
GTIN	4067923024946
Weight per piece (including packing)	90.2 g
Weight per piece (excluding packing)	90.2 g
Country of origin	CN

HC-CME-DD-107-F-SNAP-L - Conductor connector

1549644

<https://www.phoenixcontact.com/in/products/1549644>



Technical data

Notes

General	Connectors may be operated only when there is no load/voltage.
General	It is imperative that the supplied funnel pads (HC-DD...-FP) are used to prevent tip collision due to misalignment.

Mounting

Assembly note	Use within a control cabinet that is protected against unauthorized access is essential to ensure correct use. At the installation location in the control cabinet, the cable bundle to be connected must be properly installed and fitted with strain relief. As the pin connector pattern does not provide a leading protective conductor contact (PE), consistent grounding must be ensured by the control cabinet assembly.
---------------	---

Product properties

Product type	Contact insert with a fixed no. of positions
Number of positions	107
Connection profile	107+PE
Number of connections per position	1
Contact material type	turned
	rolled

Insulation characteristics

Ovvoltage category	III
Degree of pollution	3

Dimensions

Mechanical characteristics	
Contact diameter	1.6 mm

Connection data

Connection technology	
Connection technology	Crimp connection
Number of connections per position	1

Conductor connection	
Conductor cross section	0.14 mm ² ... 2.5 mm ²
Connection cross section AWG	26 ... 14
Stripping length of the individual wire	8 mm (0.14 mm ² ... 1.5 mm ²)
	6 mm (2.5 mm ²)

Electrical properties

Rated voltage (III/3)	250 V
Rated surge voltage	4 kV

HC-CME-DD-107-F-SNAP-L - Conductor connector

1549644

<https://www.phoenixcontact.com/in/products/1549644>



Rated current	10 A
---------------	------

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)
---------------------------------	--

HC-CME-DD-107-F-SNAP-L - Conductor connector




1549644

<https://www.phoenixcontact.com/in/products/1549644>

Drawings

Dimensional drawing




HC-CME-DD-107-F-SNAP-L - Conductor connector

1549644

<https://www.phoenixcontact.com/in/products/1549644>



Schematic diagram



Connector pin assignment, connection side

HC-CME-DD-107-F-SNAP-L - Conductor connector

1549644

<https://www.phoenixcontact.com/in/products/1549644>



Classifications

ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

ETIM

ETIM 9.0	EC000438
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

HC-CME-DD-107-F-SNAP-L - Conductor connector

1549644

<https://www.phoenixcontact.com/in/products/1549644>



Environmental product compliance

EU RoHS

Fulfils EU RoHS substance requirements	Yes, No exemptions
--	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in