

# BPC 120 C 25 OG - Connector

1571083

<https://www.phoenixcontact.com/us/products/1571083>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Range of articles: BPC 120, color: orange, number of positions: 1, rated voltage: 1500 V DC, rated current: 120 A, Connection method: Crimp, min. cable diameter: 7.2 mm, max. cable diameter: 12.4 mm

## Your advantages

- Patented design, with 3 proofs and one rotation
- Safety lock
- 360° free rotation and flexible wiring
- Foolproof mechanism installed
- Touch-proof
- Mismatching and short circuit proof

## Commercial data

Item number	1571083
Packing unit	15 pc
Minimum order quantity	15 pc
Sales key	AB04
Product key	ABLDBA
GTIN	4067923058279
Weight per piece (including packing)	48.08 g
Weight per piece (excluding packing)	37.2 g
Customs tariff number	85359000
Country of origin	CN

## Technical data

### Notes

#### Safety note

##### Safety note

- **WARNING:** Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
- **WARNING:** Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
- WARNING:** The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.
- The products are suitable for applications in plant, controller, and electrical device engineering.
- Assembled products may not be manipulated or improperly opened.
- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).
- When using the product in direct connection with third-party manufacturers, the user is responsible.
- For operating voltages > 50 V AC, conductive connector housings must be grounded
- Ensure that the protective or functional ground has been properly connected.
- Observe the corresponding technical data. You will find information:
  - o On the product
  - o On the packing label
  - o In the supplied documentation
  - o Online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) under the product
- The installation notes/Design In documents online on the download page at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) must be observed for this product.
- Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
- Operate the connector only when it is fully plugged in and interlocked.
- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

# BPC 120 C 25 OG - Connector



1571083

<https://www.phoenixcontact.com/us/products/1571083>

- Observe the minimum bending radius of the cable. Lay the cable without twisting it.

## Product properties

Product type	Connectors for energy storage
Product family	BPC 120
Number of positions	1

## Insulation characteristics

Degree of pollution	2
---------------------	---

## Electrical properties

Rated voltage (III/2)	1500 V DC
Nominal voltage ATD	1500 V DC (III/2.00)
	1000 V AC (III/2.00)
Rated current	120 A (with 25 mm <sup>2</sup> conductor cross-section, in accordance with IEC 61984)
	76 A (with 16 mm <sup>2</sup> conductor cross-section, in accordance with IEC 61984)
	120 A (with AWG 4, in accordance with UL 4128)
Contact resistance	≤ 0.5 mΩ
Insulation resistance	1000 MΩ
Nominal voltage U <sub>N</sub>	1500 V DC

## Connection data

Connection method	Crimp
-------------------	-------

## Material specifications

Color	orange
Material	Polyamide (Housing)
	Rubber (Seal)
Flammability rating according to UL 94	V0
Seal material	Rubber
Insulating material	PA
Contact material	Copper alloy
Contact surface material	Ni/Ag, Sn

## Cable/line

External cable diameter	7.2 mm ... 12.4 mm
Halogen-free	yes

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	100
Insertion force	≤ 75 N
Withdrawal force	≥ 10 N

# BPC 120 C 25 OG - Connector



1571083

<https://www.phoenixcontact.com/us/products/1571083>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65/IP67 (Mating socket)
Ambient temperature (operation)	-40 °C ... 125 °C (incl. temperature increase)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	4000 m

## Standards and regulations

Standard designation	TÜV (PPP 51090B)
Standards/specifications	UL 4128

# BPC 120 C 25 OG - Connector





1571083

<https://www.phoenixcontact.com/us/products/1571083>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1571083>

 <b>UL Recognized</b> Approval ID: E511681 V1S4				
	Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
keine				
	1500 V	120 A	- 4	-

 <b>TÜV SÜD Type tested</b> Approval ID: 704072474902-01				
	Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
keine				
	1500 V	120 A	-	16 - 25

# BPC 120 C 25 OG - Connector



1571083

<https://www.phoenixcontact.com/us/products/1571083>

## Classifications

### ECLASS

ECLASS-13.0	27440209
ECLASS-15.0	27440209

### ETIM

ETIM 9.0	EC002641
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# BPC 120 C 25 OG - Connector

1571083

<https://www.phoenixcontact.com/us/products/1571083>



## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)