

US-PML-W100 (100X100) - Warning label



1014127

<https://www.phoenixcontact.com/us/products/1014127>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Warning label, Card, yellow/black, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, Number of individual labels: 1, text field height: 100 mm, text field width: 100 mm

Your advantages

- UniSheet - stick-on warning labels, unmarked
- Suitable for indoor and outdoor use
- The warning labels conform to the ISO 7010 international standard
- Highly flexible, soft PVC label that adapts well to uneven surfaces

Commercial data

Item number	1014127
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2619
GTIN	4046356786409
Weight per piece (including packing)	5.99 g
Weight per piece (excluding packing)	5.99 g
Customs tariff number	39199080
Country of origin	DE

US-PML-W100 (100X100) - Warning label



1014127

<https://www.phoenixcontact.com/us/products/1014127>

Technical data

Product properties

Product type	Plant marker
Area of application	Warning identification according to ISO 7010
Type	Triangle

Marking

Number of individual labels	1
Identification technology	Thermal transfer

Dimensions

Width	92.31 mm
Height	81.35 mm
Depth	0.08 mm

Material specifications

Foil strength	60 µm
Adhesive strength	25 µm
Adhesive	Acrylic
Color	yellow/black
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
---------------	--------------------------------------

US-PML-W100 (100X100) - Warning label



1014127

<https://www.phoenixcontact.com/us/products/1014127>

	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (assembly)	> 10 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Mounting

Mounting type	adhesive
---------------	----------

US-PML-W100 (100X100) - Warning label



1014127

<https://www.phoenixcontact.com/us/products/1014127>

Classifications

ECLASS

ECLASS-15.0	40200203
ECLASS-13.0	40200203

ETIM

ETIM 9.0	EC001777
----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

US-PML-W100 (100X100) - Warning label



1014127

<https://www.phoenixcontact.com/us/products/1014127>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com