

FL SWITCH SFNB 8TX-PNE - Industrial Ethernet Switch



1071800

<https://www.phoenixcontact.com/us/products/1071800>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ethernet switch, eight TP RJ45 ports, automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function. The multicast filter will block PROFINET PTCP-Delay traffic. EtherNet/IP™-based traffic will be prioritized over standard traffic.

Your advantages

- QoS-prioritized (Quality of Service) messages
- RJ45 ports support a transmission speed of 10/100 Mbps
- Local diagnostic indicators with LEDs
- Auto negotiation and autocrossing detection simplifies installation and setup

Commercial data

Item number	1071800
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN19
Product key	DNN113
GTIN	4055626758985
Weight per piece (including packing)	410 g
Weight per piece (excluding packing)	400 g
Country of origin	TW

FL SWITCH SFNB 8TX-PNE - Industrial Ethernet Switch



1071800

<https://www.phoenixcontact.com/us/products/1071800>

Technical data

Dimensions

Width	50 mm
Height	110 mm
Depth	70 mm

Material specifications

Housing material	Aluminum
------------------	----------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Interfaces

Ethernet (RJ45)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	8 (RJ45 ports)

Product properties

Product type	Switch
Product family	Unmanaged Switch SFNB
Type	Block design
MTTF	253.4 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode

Switch functions

EtherNet/IP™ supported protocols	EtherNet/IP™
Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode
PROFINET conformance class	Conformance Class A
MAC address table	2k
Status and diagnostic indicators	LEDs: U _S , link and activity per port
Additional functions	Autonegotiation

Security functions

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode
-----------------	---

FL SWITCH SFNB 8TX-PNE - Industrial Ethernet Switch



1071800

<https://www.phoenixcontact.com/us/products/1071800>

Electrical properties

Maximum power dissipation for nominal condition	3.36 W
Transmission medium	Copper

Supply

Supply voltage (DC)	24 V DC
Supply voltage range	9 V DC ... 32 V DC
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm ²
Residual ripple	3.6 V _{pp} (within the permitted voltage range)
Max. current consumption	380 mA (at 9 V DC)
Typical current consumption	140 mA (at U _S = 24 V DC)

Connection data

Connection technology

Connection name	Power supply
pluggable	yes

Power supply

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (up to 1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Noise immunity	EN 61000-6-2:2005

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

System properties

Functionality

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3,
-----------------	--

FL SWITCH SFNB 8TX-PNE - Industrial Ethernet Switch



1071800
<https://www.phoenixcontact.com/us/products/1071800>

	store and forward switching mode
--	----------------------------------

Signaling

Status display	LEDs: U _S , link and activity per port
----------------	---

FL SWITCH SFNB 8TX-PNE - Industrial Ethernet Switch



1071800

<https://www.phoenixcontact.com/us/products/1071800>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1071800>



IECEE CB Scheme

Approval ID: DK-88783-M1-UL



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705

FL SWITCH SFNB 8TX-PNE - Industrial Ethernet Switch



1071800
<https://www.phoenixcontact.com/us/products/1071800>

Classifications

ECLASS

ECLASS-13.0	19170402
-------------	----------

ETIM

ETIM 9.0	EC000734
----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

FL SWITCH SFNB 8TX-PNE - Industrial Ethernet Switch



1071800

<https://www.phoenixcontact.com/us/products/1071800>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com