


1088734

<https://www.phoenixcontact.com/us/products/1088734>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 1000 V, nominal current: 32 A, number of connections: 4, connection method: Push-in connection, Rated cross section: 4 mm<sup>2</sup>, cross section: 0.2 mm<sup>2</sup> - 6 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: gray

Your advantages

- Clear wiring, thanks to lateral conductor entry
- The compact design enables wiring in a confined space
- The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system
- In addition to the testing option in the double function shaft, all terminal blocks provide an additional test pick-off

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1088734       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE23          |
| Product key                          | BE2313        |
| GTIN                                 | 4055626890159 |
| Weight per piece (including packing) | 12.06 g       |
| Weight per piece (excluding packing) | 12.09 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | CN            |

# PTV 4-QUATTRO - Feed-through terminal block



1088734

<https://www.phoenixcontact.com/us/products/1088734>

## Technical data

### Notes

#### General

|      |                                                                                              |
|------|----------------------------------------------------------------------------------------------|
| Note | The max. load current must not be exceeded by the total current of all connected conductors. |
|------|----------------------------------------------------------------------------------------------|

### Product properties

|                       |                                |
|-----------------------|--------------------------------|
| Product type          | Multi-conductor terminal block |
| Product family        | PTV                            |
| Area of application   | Railway industry               |
|                       | Machine building               |
|                       | Plant engineering              |
|                       | Process industry               |
| Number of connections | 4                              |
| Number of rows        | 1                              |
| Potentials            | 1                              |

#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 1.02 W |

### Connection data

|                                                                                           |                                                              |
|-------------------------------------------------------------------------------------------|--------------------------------------------------------------|
| Number of connections per level                                                           | 4                                                            |
| Nominal cross section                                                                     | 4 mm <sup>2</sup>                                            |
| Connection method                                                                         | Push-in connection                                           |
| Stripping length                                                                          | 9 mm ... 11 mm                                               |
| Internal cylindrical gage                                                                 | A4                                                           |
| Connection in acc. with standard                                                          | IEC 60947-7-1                                                |
| Conductor cross-section rigid                                                             | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>                    |
| Cross section AWG                                                                         | 24 ... 10 (converted acc. to IEC)                            |
| Conductor cross-section flexible                                                          | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>                    |
| Conductor cross-section, flexible [AWG]                                                   | 24 ... 10 (converted acc. to IEC)                            |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>                    |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>                    |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                  |
| Nominal current                                                                           | 32 A                                                         |
| Maximum load current                                                                      | 38 A (with 6 mm <sup>2</sup> conductor cross-section, rigid) |
| Nominal voltage                                                                           | 1000 V                                                       |

# PTV 4-QUATTRO - Feed-through terminal block



1088734

<https://www.phoenixcontact.com/us/products/1088734>

|                                                                   |                    |
|-------------------------------------------------------------------|--------------------|
| Nominal cross section                                             | 4 mm²              |
| Connection cross sections directly pluggable                      |                    |
| Conductor cross-section rigid                                     | 0.75 mm² ... 6 mm² |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 1.5 mm² ... 4 mm²  |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 1.5 mm² ... 4 mm²  |

## Ex data

### Rated data (ATEX/IECEx)

|                                                    |                                     |
|----------------------------------------------------|-------------------------------------|
| Identification                                     | Ⓔ II 2 G Ex eb IIC Gb               |
| Operating temperature range                        | -60 °C ... 110 °C                   |
| Ex-certified accessories                           | 1088748 D-PTV 2,5/4-QUATTRO         |
|                                                    | 1083618 DS-PTV 2,5/4                |
|                                                    | 3047196 ATP-UT-QUATTRO              |
|                                                    | 1212587 SF-SL 0,6X3,5-100 S-VDE     |
|                                                    | 3022276 CLIPFIX 35-5                |
| List of bridges                                    | Plug-in bridge / FBS 2-6 / 3030336  |
|                                                    | Plug-in bridge / FBS 3-6 / 3030242  |
|                                                    | Plug-in bridge / FBS 4-6 / 3030255  |
|                                                    | Plug-in bridge / FBS 5-6 / 3030349  |
|                                                    | Plug-in bridge / FBS 10-6 / 3030271 |
|                                                    | Plug-in bridge / FBS 20-6 / 3030365 |
|                                                    | Plug-in bridge / FBS 50-6 / 3032224 |
| Bridge data                                        | 27 A (4 mm²)                        |
| Ex temperature increase                            | 40 K (27,6 A / 4 mm²)               |
| for bridging with bridge                           | 550 V                               |
| - At bridging between non-adjacent terminal blocks | 550 V                               |
| - At cut-to-length bridging                        | 275 V                               |
| - At cut-to-length bridging with cover             | 275 V                               |
| - At cut-to-length bridging with partition plate   | 550 V                               |
| Rated insulation voltage                           | 500 V                               |
| output                                             | (Permanent)                         |

### Ex level General

|                      |              |
|----------------------|--------------|
| Rated voltage        | 550 V        |
| Rated current        | 27 A (4 mm²) |
| Maximum load current | 31 A (6 mm²) |
| Contact resistance   | 0.7 mΩ       |

### Ex connection data General

|                              |                   |
|------------------------------|-------------------|
| Nominal cross section        | 4 mm²             |
| Rated cross section AWG      | 12                |
| Connection capacity rigid    | 0.2 mm² ... 6 mm² |
| Connection capacity AWG      | 24 ... 10         |
| Connection capacity flexible | 0.2 mm² ... 6 mm² |

# PTV 4-QUATTRO - Feed-through terminal block



1088734

<https://www.phoenixcontact.com/us/products/1088734>

|                         |           |
|-------------------------|-----------|
| Connection capacity AWG | 24 ... 10 |
|-------------------------|-----------|

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 6.2 mm  |
| End cover width    | 2.2 mm  |
| Height             | 69.2 mm |
| Depth              | 45.7 mm |
| Depth on NS 35/7,5 | 47.2 mm |
| Depth on NS 35/15  | 54.7 mm |

## Material specifications

|                                                                  |                 |
|------------------------------------------------------------------|-----------------|
| Color                                                            | gray (RAL 7042) |
| Flammability rating according to UL 94                           | V0              |
| Insulating material group                                        | I               |
| Insulating material                                              | PA              |
| Static insulating material application in cold                   | -60 °C          |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26           | HL 1 - HL 3     |
| Surface flammability NFPA 130 (ASTM E 162)                       | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)          | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                           | passed          |

## Electrical tests

### Surge voltage test

|                                                |             |
|------------------------------------------------|-------------|
| Result                                         | Test passed |
| Short-time withstand current 4 mm <sup>2</sup> | 0.48 kA     |
| Result                                         | Test passed |

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 2.2 kV      |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### Attachment on the carrier

# PTV 4-QUATTRO - Feed-through terminal block



1088734

<https://www.phoenixcontact.com/us/products/1088734>

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

## Test for conductor damage and slackening

|                                |                              |
|--------------------------------|------------------------------|
| Rotation speed                 | 10 rpm                       |
| Revolutions                    | 135                          |
| Conductor cross-section/weight | 0.2 mm <sup>2</sup> / 0.2 kg |
|                                | 4 mm <sup>2</sup> / 0.9 kg   |
|                                | 6 mm <sup>2</sup> / 1.4 kg   |
| Result                         | Test passed                  |

## Environmental and real-life conditions

### Aging

|                    |             |
|--------------------|-------------|
| Temperature cycles | 192         |
| Result             | Test passed |

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |                                                |
|------------------------|------------------------------------------------|
| Specification          | DIN EN 50155 (VDE 0115-200):2018-05            |
| Spectrum               | Long life test category 2, bogie-mounted       |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level              | 6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz      |
| Acceleration           | 3.12g                                          |
| Test duration per axis | 5 h                                            |
| Test directions        | X-, Y- and Z-axis                              |
| Result                 | Test passed                                    |

### Shocks

|                                |                                   |
|--------------------------------|-----------------------------------|
| Pulse shape                    | Half-sine                         |
| Acceleration                   | 30g                               |
| Shock duration                 | 18 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |
| Result                         | Test passed                       |

### Ambient conditions

|                                          |                                                                                                                              |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)                                                    |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                                                                              |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                                                                              |
| Permissible humidity (operation)         | 20 % ... 90 %                                                                                                                |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                                                                                |

# PTV 4-QUATTRO - Feed-through terminal block



1088734

<https://www.phoenixcontact.com/us/products/1088734>

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# PTV 4-QUATTRO - Feed-through terminal block




1088734

<https://www.phoenixcontact.com/us/products/1088734>

## Drawings

Circuit diagram



# PTV 4-QUATTRO - Feed-through terminal block



1088734

<https://www.phoenixcontact.com/us/products/1088734>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1088734>

|  <b>CSA</b><br>Approval ID: 158887 |                       |                       |                   |                             |
|---------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                     | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                   | 600 V                 | 30 A                  | 26 - 10           | -                           |
| C                                                                                                                   | 600 V                 | 30 A                  | 26 - 10           | -                           |
| D                                                                                                                   | 600 V                 | 5 A                   | 26 - 10           | -                           |

|  <b>IECEE CB Scheme</b><br>Approval ID: DE1-67139 |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                    | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                              | 1000 V                | 32 A                  | -                 | 0.2 - 6                     |

|  <b>EAC</b><br>Approval ID: RU C-DE.BL08.B.00644 |  |  |  |  |
|-------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
|-------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                    | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                                  | 600 V                 | 30 A                  | 26 - 10           | -                           |
| C                                                                                                                                  | 600 V                 | 30 A                  | 26 - 10           | -                           |
| F                                                                                                                                  | 1000 V                | 30 A                  | 26 - 10           | -                           |

|  <b>VDE Zeichengenehmigung</b><br>Approval ID: 40056318 |                       |                       |                   |                             |
|--------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                            | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                                      | 1000 V                | 32 A                  | -                 | 0.2 - 6                     |

|  <b>IECEx</b><br>Approval ID: IECExPTB20.0037U |  |  |  |  |
|-----------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
|-----------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|

# PTV 4-QUATTRO - Feed-through terminal block



1088734

<https://www.phoenixcontact.com/us/products/1088734>



**ATEX**

Approval ID: PTB20ATEX1016U



**CCC**

Approval ID: 2021122313114374



**UKCA-EX**

Approval ID: CSAE 22UKEX1099U



**EAC Ex**

Approval ID: KZ 7500525010101950

# PTV 4-QUATTRO - Feed-through terminal block



1088734

<https://www.phoenixcontact.com/us/products/1088734>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
| ECLASS-15.0 | 27250101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PTV 4-QUATTRO - Feed-through terminal block



1088734

<https://www.phoenixcontact.com/us/products/1088734>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)