

1625625

<https://www.phoenixcontact.com/us/products/1625625>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Rear panel feed-through, series: UC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, Axial O-ring, cable diameter range: 6.5 mm ... 14.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1625625
Packing unit	12 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAIJ
GTIN	4046356877237
Weight per piece (including packing)	141.44 g
Weight per piece (excluding packing)	139.76 g
Country of origin	DE

UC-17S1N8AQPAD - Rear panel feed-through



1625625

<https://www.phoenixcontact.com/us/products/1625625>

Technical data

Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Number Contact (Contact group 1)	17
Diameter Contact (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Order information:	Order contact inserts separately
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	Pg16
Mounting type	Rear mounting (Pg16)
Assembly note	Central fastening
Housing material	Metal
Degree of protection (plugged in)	IP67
Seal for the device	Axial O-ring

Seal

External cable diameter	6.5 mm ... 14.5 mm
-------------------------	--------------------

Environmental and real-life conditions

UC-17S1N8AQPAD - Rear panel feed-through



1625625

<https://www.phoenixcontact.com/us/products/1625625>

Ambient conditions

Permissible humidity (storage/transport)
--

50 % ... 65 %

UC-17S1N8AQPAD - Rear panel feed-through


1625625

<https://www.phoenixcontact.com/us/products/1625625>



Drawings

Schematic diagram



Connector pin assignment

UC-17S1N8AQPAD - Rear panel feed-through



1625625

<https://www.phoenixcontact.com/us/products/1625625>

Classifications

ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UC-17S1N8AQPAD - Rear panel feed-through



1625625

<https://www.phoenixcontact.com/us/products/1625625>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	919d27a0-bdd0-46c8-bfde-dcd6c63aba49

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com